

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844228

Luminaire Tested: **LD6C25DE010B2750 EU6C25B35 6LBNLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C25DE010B2750 EU6C25B35 6LBNLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2046.6 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844228

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B35 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P844228

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B35 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89				89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85				85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80				80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76				76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72				72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68				68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65				65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62				62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59				59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	255429
5°	238867
10°	194819
15°	143366
20°	98814
25°	73359
30°	55103
35°	34365
40°	16681
45°	5722
50°	751
55°	564
60°	329
65°	389
70°	481
75°	0
80°	0
85°	0



TEST NUMBER: P844228

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B35 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.4	18.9
10°-20°	695.4	34.0
20°-30°	562.2	27.5
30°-40°	323.9	15.8
40°-50°	68.5	3.3
50°-60°	5.9	0.3
60°-70°	3.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1645.0	80.4
0°-40°	1968.8	96.2
0°-60°	2043.2	99.8
0°-90°	2046.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2046.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4659	
5°	4341	387
15°	2526	695
25°	1213	562
35°	514	324
45°	74	68
55°	6	6
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P844228

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B35 6LBNLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4659.4
2.5°	4603.5
5°	4340.7
7.5°	3963.1
10°	3499.8
12.5°	3024.7
15°	2526.1
17.5°	2045.0
20°	1693.8
22.5°	1425.3
25°	1212.8
27.5°	1032.9
30°	870.5
32.5°	690.5
35°	513.5
37.5°	357.1
40°	233.1
42.5°	141.7
45°	73.8
47.5°	29.5
50°	8.8
52.5°	8.8
55°	5.9
57.5°	5.9
60°	3.0
62.5°	3.0
65°	3.0
67.5°	3.0
70°	3.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)