

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844252

Luminaire Tested: **LD6C25DE010B2750 EU6C25B50 6LBCSMW**

Issue Date: 5/7/2024

Test Information

Test Method: LM-79-08
Report Number: P844252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C25DE010B2750 EU6C25B50 6LBSCMW
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2993.1 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844252

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B50 6LBCSMW

Luminous Intensity Polar Plot





TEST NUMBER: P844252

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B50 6LBSCMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 110 | 106 | 102 | 99 | 108 | 104 | 100 | 97 | 100 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 89 | 87 | | | | 87 |
| 2 | 101 | 94 | 87 | 82 | 99 | 92 | 86 | 81 | 88 | 84 | 79 | 85 | 81 | 78 | 82 | 79 | 76 | 74 | | | | 74 |
| 3 | 93 | 83 | 75 | 70 | 90 | 81 | 74 | 69 | 79 | 73 | 68 | 76 | 71 | 67 | 73 | 69 | 65 | 63 | | | | 63 |
| 4 | 85 | 74 | 66 | 60 | 83 | 73 | 65 | 59 | 70 | 64 | 58 | 68 | 62 | 58 | 66 | 61 | 57 | 55 | | | | 55 |
| 5 | 79 | 66 | 58 | 52 | 77 | 65 | 57 | 51 | 63 | 56 | 51 | 61 | 55 | 50 | 60 | 54 | 50 | 48 | | | | 48 |
| 6 | 73 | 60 | 52 | 45 | 71 | 59 | 51 | 45 | 57 | 50 | 45 | 56 | 49 | 44 | 54 | 49 | 44 | 42 | | | | 42 |
| 7 | 68 | 55 | 46 | 40 | 66 | 54 | 46 | 40 | 52 | 45 | 40 | 51 | 44 | 40 | 50 | 44 | 39 | 37 | | | | 37 |
| 8 | 63 | 50 | 42 | 36 | 61 | 49 | 41 | 36 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 35 | 33 | | | | 33 |
| 9 | 59 | 46 | 38 | 33 | 57 | 45 | 38 | 32 | 44 | 37 | 32 | 43 | 37 | 32 | 42 | 36 | 32 | 30 | | | | 30 |
| 10 | 55 | 42 | 35 | 30 | 54 | 42 | 34 | 30 | 41 | 34 | 29 | 40 | 34 | 29 | 39 | 33 | 29 | 27 | | | | 27 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 67023 |
| 5° | 66971 |
| 10° | 66938 |
| 15° | 66306 |
| 20° | 65823 |
| 25° | 65169 |
| 30° | 64054 |
| 35° | 63008 |
| 40° | 61143 |
| 45° | 59068 |
| 50° | 55546 |
| 55° | 50283 |
| 60° | 44130 |
| 65° | 37164 |
| 70° | 29075 |
| 75° | 20376 |
| 80° | 11428 |
| 85° | 7925 |



TEST NUMBER: P844252

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B50 6LBCSMW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 115.8 | 3.9 |
| 10°-20° | 329.8 | 11.0 |
| 20°-30° | 496.0 | 16.6 |
| 30°-40° | 587.9 | 19.6 |
| 40°-50° | 585.0 | 19.5 |
| 50°-60° | 471.6 | 15.8 |
| 60°-70° | 285.2 | 9.5 |
| 70°-80° | 106.0 | 3.5 |
| 80°-90° | 15.7 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 941.6 | 31.5 |
| 0°-40° | 1529.5 | 51.1 |
| 0°-60° | 2586.2 | 86.4 |
| 0°-90° | 2993.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2993.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1223 | |
| 5° | 1217 | 116 |
| 15° | 1168 | 330 |
| 25° | 1077 | 496 |
| 35° | 942 | 588 |
| 45° | 762 | 585 |
| 55° | 526 | 472 |
| 65° | 286 | 285 |
| 75° | 96 | 106 |
| 85° | 13 | 16 |
| 90° | 0 | |



TEST NUMBER: P844252

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B50 6LBSCMW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1222.6 |
| 2.5° | 1222.6 |
| 5° | 1217.0 |
| 7.5° | 1213.5 |
| 10° | 1202.5 |
| 12.5° | 1184.3 |
| 15° | 1168.3 |
| 17.5° | 1150.0 |
| 20° | 1128.3 |
| 22.5° | 1106.3 |
| 25° | 1077.4 |
| 27.5° | 1046.5 |
| 30° | 1011.9 |
| 32.5° | 979.6 |
| 35° | 941.5 |
| 37.5° | 901.5 |
| 40° | 854.4 |
| 42.5° | 808.8 |
| 45° | 761.9 |
| 47.5° | 709.1 |
| 50° | 651.3 |
| 52.5° | 591.2 |
| 55° | 526.1 |
| 57.5° | 467.9 |
| 60° | 402.5 |
| 62.5° | 344.7 |
| 65° | 286.5 |
| 67.5° | 232.0 |
| 70° | 181.4 |
| 72.5° | 136.1 |
| 75° | 96.2 |
| 77.5° | 61.7 |
| 80° | 36.2 |
| 82.5° | 21.7 |
| 85° | 12.6 |
| 87.5° | 5.4 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)