

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245331

Luminaire Tested: **LSR8B30D010 EC8B30840 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30840 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3432.1 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245331

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245331

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59943
5°	60172
10°	60930
15°	62121
20°	63009
25°	63268
30°	61329
35°	55977
40°	48421
45°	38119
50°	24591
55°	12069
60°	4965
65°	2174
70°	631
75°	238
80°	178
85°	0



TEST NUMBER: P245331

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.6	5.4
10°-20°	549.9	16.0
20°-30°	851.4	24.8
30°-40°	922.4	26.9
40°-50°	663.7	19.3
50°-60°	222.1	6.5
60°-70°	33.6	1.0
70°-80°	2.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1587.0	46.2
0°-40°	2509.4	73.1
0°-60°	3395.2	98.9
0°-90°	3432.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3432.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1944	
5°	1944	186
15°	1946	550
25°	1860	851
35°	1487	922
45°	874	664
55°	224	222
65°	30	34
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245331

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1943.9
2.5°	1943.9
5°	1943.9
7.5°	1944.9
10°	1945.9
12.5°	1947.9
15°	1945.9
17.5°	1938.0
20°	1920.1
22.5°	1893.3
25°	1859.5
27.5°	1805.9
30°	1722.4
32.5°	1613.2
35°	1487.0
37.5°	1350.9
40°	1202.9
42.5°	1044.0
45°	874.1
47.5°	690.4
50°	512.6
52.5°	351.6
55°	224.5
57.5°	134.1
60°	80.5
62.5°	48.7
65°	29.8
67.5°	14.9
70°	7.0
72.5°	3.0
75°	2.0
77.5°	2.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)