

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844312

Luminaire Tested: **LD6C30DE010B2750 EU6C30B35 6LBNH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844312  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C30DE010B2750 EU6C30B35 6LBNH  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1802.3 lumens  
Efficiency: N/A  
Efficacy: 52.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 34.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844312

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P844312

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126651
5°	123514
10°	113970
15°	100903
20°	87607
25°	74938
30°	61782
35°	40683
40°	21877
45°	9683
50°	3923
55°	2829
60°	1798
65°	1284
70°	1074
75°	699
80°	1042
85°	0



TEST NUMBER: P844312

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	207.8	11.5
10°-20°	495.4	27.5
20°-30°	567.6	31.5
30°-40°	381.3	21.2
40°-50°	108.9	6.0
50°-60°	26.7	1.5
60°-70°	10.2	0.6
70°-80°	3.9	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1270.8	70.5
0°-40°	1652.1	91.7
0°-60°	1787.7	99.2
0°-90°	1802.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1802.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2310	
5°	2244	208
15°	1778	495
25°	1239	568
35°	608	381
45°	125	109
55°	30	27
65°	10	10
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P844312

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2310.3
2.5°	2293.8
5°	2244.5
7.5°	2155.8
10°	2047.4
12.5°	1909.2
15°	1777.9
17.5°	1639.9
20°	1501.7
22.5°	1370.4
25°	1238.9
27.5°	1117.3
30°	976.0
32.5°	788.7
35°	607.9
37.5°	443.6
40°	305.7
42.5°	200.4
45°	124.9
47.5°	75.5
50°	46.0
52.5°	36.2
55°	29.6
57.5°	23.1
60°	16.4
62.5°	13.1
65°	9.9
67.5°	6.7
70°	6.7
72.5°	3.3
75°	3.3
77.5°	3.3
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)