

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244251

Luminaire Tested: **LSR8B30D010 EC8B30840 8LBW0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30840 8LBW0H
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3081.0 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244251

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P244251

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	71	77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59	68	62	58	66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63705
5°	63564
10°	62987
15°	63222
20°	63091
25°	62475
30°	59545
35°	51557
40°	36776
45°	22603
50°	14910
55°	9860
60°	6315
65°	3444
70°	1686
75°	846
80°	479
85°	318



TEST NUMBER: P244251

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	6.3
10°-20°	558.6	18.1
20°-30°	840.6	27.3
30°-40°	832.3	27.0
40°-50°	422.9	13.7
50°-60°	170.3	5.5
60°-70°	51.6	1.7
70°-80°	8.9	0.3
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1593.9	51.7
0°-40°	2426.2	78.7
0°-60°	3019.4	98.0
0°-90°	3081.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3081.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2066	
5°	2054	195
15°	1980	559
25°	1836	841
35°	1370	832
45°	518	423
55°	183	170
65°	47	52
75°	7	9
85°	1	1
90°	0	



TEST NUMBER: P244251

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2065.9
1°	2061.5
2°	2057.9
3°	2057.0
4°	2056.1
5°	2053.5
6°	2049.9
7°	2042.8
8°	2032.1
9°	2022.3
10°	2011.6
11°	2002.7
12°	1996.5
13°	1992.0
14°	1986.7
15°	1980.4
16°	1972.4
17°	1962.6
18°	1951.1
19°	1937.7
20°	1922.6
21°	1906.5
22°	1890.5
23°	1873.6
24°	1855.8
25°	1836.2
26°	1814.8
27°	1787.2
28°	1755.2
29°	1716.9
30°	1672.3
32.5°	1542.3
35°	1369.6
37.5°	1154.1
40°	913.6
42.5°	690.1
45°	518.3
47.5°	396.3
50°	310.8
52.5°	241.3
55°	183.4
57.5°	136.2
60°	102.4
62.5°	73.0
65°	47.2



TEST NUMBER: P244251

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	29.4
70°	18.7
72.5°	11.6
75°	7.1
77.5°	4.5
80°	2.7
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)