

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246555

Luminaire Tested: **LSR8B30D010 EC8B30840 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30840 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3132.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246555

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246555

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 99 | 101 | 99 | 96 | 97 | 95 | 93 | 94 | 92 | 91 | 89 |
| 2 | 103 | 97 | 91 | 87 | 101 | 95 | 90 | 86 | 92 | 87 | 84 | 88 | 85 | 82 | 86 | 83 | 80 | 78 |
| 3 | 96 | 88 | 81 | 76 | 94 | 86 | 80 | 75 | 83 | 78 | 74 | 81 | 76 | 73 | 78 | 75 | 72 | 70 |
| 4 | 90 | 80 | 73 | 67 | 88 | 79 | 72 | 67 | 76 | 70 | 66 | 74 | 69 | 65 | 72 | 68 | 64 | 62 |
| 5 | 84 | 73 | 66 | 60 | 82 | 72 | 65 | 60 | 70 | 64 | 59 | 68 | 63 | 59 | 67 | 62 | 58 | 56 |
| 6 | 79 | 67 | 60 | 54 | 77 | 66 | 59 | 54 | 65 | 58 | 54 | 63 | 58 | 53 | 62 | 57 | 53 | 51 |
| 7 | 74 | 62 | 55 | 49 | 72 | 61 | 54 | 49 | 60 | 54 | 49 | 59 | 53 | 49 | 57 | 52 | 48 | 47 |
| 8 | 69 | 58 | 50 | 45 | 68 | 57 | 50 | 45 | 56 | 50 | 45 | 55 | 49 | 45 | 54 | 48 | 45 | 43 |
| 9 | 65 | 54 | 47 | 42 | 64 | 53 | 46 | 42 | 52 | 46 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 40 |
| 10 | 62 | 50 | 43 | 39 | 61 | 50 | 43 | 39 | 49 | 43 | 38 | 48 | 42 | 38 | 47 | 42 | 38 | 37 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 63992 |
| 5° | 62914 |
| 10° | 60933 |
| 15° | 59526 |
| 20° | 58677 |
| 25° | 57525 |
| 30° | 54012 |
| 35° | 44089 |
| 40° | 27312 |
| 45° | 18499 |
| 50° | 16296 |
| 55° | 15381 |
| 60° | 15258 |
| 65° | 14783 |
| 70° | 13253 |
| 75° | 11485 |
| 80° | 9696 |
| 85° | 7748 |



TEST NUMBER: P246555

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 191.2 | 6.1 |
| 10°-20° | 526.6 | 16.8 |
| 20°-30° | 772.3 | 24.7 |
| 30°-40° | 705.9 | 22.5 |
| 40°-50° | 349.5 | 11.2 |
| 50°-60° | 258.4 | 8.3 |
| 60°-70° | 198.6 | 6.3 |
| 70°-80° | 103.6 | 3.3 |
| 80°-90° | 25.8 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1490.1 | 47.6 |
| 0°-40° | 2196.0 | 70.1 |
| 0°-60° | 2804.0 | 89.5 |
| 0°-90° | 3132.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3132.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2075 | |
| 5° | 2032 | 191 |
| 15° | 1865 | 527 |
| 25° | 1691 | 772 |
| 35° | 1171 | 706 |
| 45° | 424 | 350 |
| 55° | 286 | 258 |
| 65° | 203 | 199 |
| 75° | 96 | 104 |
| 85° | 22 | 26 |
| 90° | 0 | |



TEST NUMBER: P246555

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBW0MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2075.2 |
| 2.5° | 2064.2 |
| 5° | 2032.5 |
| 7.5° | 1989.7 |
| 10° | 1946.0 |
| 12.5° | 1903.3 |
| 15° | 1864.6 |
| 17.5° | 1827.8 |
| 20° | 1788.1 |
| 22.5° | 1743.4 |
| 25° | 1690.7 |
| 27.5° | 1618.2 |
| 30° | 1516.9 |
| 32.5° | 1374.8 |
| 35° | 1171.2 |
| 37.5° | 918.9 |
| 40° | 678.5 |
| 42.5° | 513.6 |
| 45° | 424.2 |
| 47.5° | 375.5 |
| 50° | 339.7 |
| 52.5° | 310.9 |
| 55° | 286.1 |
| 57.5° | 265.2 |
| 60° | 247.4 |
| 62.5° | 228.5 |
| 65° | 202.6 |
| 67.5° | 174.8 |
| 70° | 147.0 |
| 72.5° | 121.2 |
| 75° | 96.4 |
| 77.5° | 74.5 |
| 80° | 54.6 |
| 82.5° | 37.7 |
| 85° | 21.9 |
| 87.5° | 7.9 |
| 90° | 0.0 |

(END OF REPORT)