

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844316

Luminaire Tested: **LD6C30DE010B2750 EU6C30B35 6LBWH**

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P844316  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C30DE010B2750 EU6C30B35 6LBWH  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2534.0 lumens  
Efficiency: N/A  
Efficacy: 74.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 34.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844316

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P844316

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	85684
5°	85648
10°	84991
15°	84422
20°	83138
25°	81235
30°	76486
35°	69225
40°	57801
45°	44291
50°	31368
55°	19775
60°	11150
65°	7238
70°	4728
75°	3474
80°	2084
85°	2076



TEST NUMBER: P844316

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.6	5.8
10°-20°	418.9	16.5
20°-30°	614.2	24.2
30°-40°	639.2	25.2
40°-50°	442.2	17.5
50°-60°	192.5	7.6
60°-70°	59.0	2.3
70°-80°	17.7	0.7
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1180.7	46.6
0°-40°	1819.9	71.8
0°-60°	2454.6	96.9
0°-90°	2534.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2534.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1563	
5°	1556	148
15°	1488	419
25°	1343	614
35°	1034	639
45°	571	442
55°	207	193
65°	56	59
75°	16	18
85°	3	3
90°	0	



TEST NUMBER: P844316

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B35 6LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1563.0
2.5°	1566.2
5°	1556.4
7.5°	1543.3
10°	1526.8
12.5°	1510.4
15°	1487.5
17.5°	1457.8
20°	1425.1
22.5°	1389.0
25°	1343.0
27.5°	1283.9
30°	1208.3
32.5°	1129.6
35°	1034.4
37.5°	929.3
40°	807.7
42.5°	686.3
45°	571.3
47.5°	462.9
50°	367.8
52.5°	279.1
55°	206.9
57.5°	147.8
60°	101.7
62.5°	75.5
65°	55.8
67.5°	42.7
70°	29.5
72.5°	23.1
75°	16.4
77.5°	9.8
80°	6.6
82.5°	3.3
85°	3.3
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)