

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246633

Luminaire Tested: **LSR8B30D010 EC8B30850 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30850 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2885.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246633

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246633

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93295
5°	92624
10°	84408
15°	72350
20°	64118
25°	57218
30°	46207
35°	32062
40°	20344
45°	15111
50°	12900
55°	11306
60°	10120
65°	9040
70°	7790
75°	7160
80°	6677
85°	5909



TEST NUMBER: P246633

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.0	9.6
10°-20°	638.4	22.1
20°-30°	759.2	26.3
30°-40°	536.7	18.6
40°-50°	277.0	9.6
50°-60°	189.9	6.6
60°-70°	123.3	4.3
70°-80°	64.6	2.2
80°-90°	19.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1673.6	58.0
0°-40°	2210.2	76.6
0°-60°	2677.2	92.8
0°-90°	2885.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2885.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3026	
5°	2992	276
15°	2266	638
25°	1682	759
35°	852	537
45°	346	277
55°	210	190
65°	124	123
75°	60	65
85°	17	19
90°	0	1
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246633

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3025.5
2.5°	3025.5
5°	2992.3
7.5°	2882.3
10°	2695.7
12.5°	2473.1
15°	2266.3
17.5°	2096.1
20°	1953.9
22.5°	1819.5
25°	1681.7
27.5°	1508.7
30°	1297.7
32.5°	1070.8
35°	851.7
37.5°	656.2
40°	505.4
42.5°	406.7
45°	346.5
47.5°	302.8
50°	268.9
52.5°	239.1
55°	210.3
57.5°	185.0
60°	164.1
62.5°	142.2
65°	123.9
67.5°	107.4
70°	86.4
72.5°	74.2
75°	60.1
77.5°	48.8
80°	37.6
82.5°	28.0
85°	16.7
87.5°	9.6
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246633

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)