

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245769

Luminaire Tested: **LSR8B30D010 EC8B30850 8LBSOGPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30850 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3104.0 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245769

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245769

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54941
5°	54773
10°	54236
15°	53677
20°	53115
25°	52247
30°	50818
35°	48501
40°	45096
45°	38075
50°	25853
55°	13505
60°	6062
65°	2955
70°	1190
75°	727
80°	533
85°	354



TEST NUMBER: P245769

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.7	5.4
10°-20°	474.3	15.3
20°-30°	706.0	22.7
30°-40°	802.5	25.9
40°-50°	656.2	21.1
50°-60°	244.6	7.9
60°-70°	44.7	1.4
70°-80°	6.9	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1348.0	43.4
0°-40°	2150.5	69.3
0°-60°	3051.4	98.3
0°-90°	3104.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3104.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1782	
5°	1770	168
15°	1681	474
25°	1536	706
35°	1288	803
45°	873	656
55°	251	245
65°	40	45
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P245769

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1781.7
2.5°	1778.7
5°	1769.5
7.5°	1753.3
10°	1732.1
12.5°	1707.7
15°	1681.4
17.5°	1651.0
20°	1618.6
22.5°	1580.1
25°	1535.6
27.5°	1484.9
30°	1427.2
32.5°	1361.3
35°	1288.4
37.5°	1210.4
40°	1120.3
42.5°	1008.8
45°	873.1
47.5°	710.0
50°	538.9
52.5°	379.8
55°	251.2
57.5°	158.0
60°	98.3
62.5°	62.8
65°	40.5
67.5°	23.3
70°	13.2
72.5°	8.1
75°	6.1
77.5°	4.1
80°	3.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)