

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245355

Luminaire Tested: **LSR8B30D010 EC8B30935 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30935 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2946.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245355

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245355

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51457
5°	51653
10°	52304
15°	53326
20°	54086
25°	54309
30°	52645
35°	48049
40°	41566
45°	32720
50°	21108
55°	10360
60°	4262
65°	1868
70°	541
75°	203
80°	160
85°	0



TEST NUMBER: P245355

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.4	5.4
10°-20°	472.1	16.0
20°-30°	730.9	24.8
30°-40°	791.7	26.9
40°-50°	569.7	19.3
50°-60°	190.6	6.5
60°-70°	28.8	1.0
70°-80°	2.5	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1362.3	46.2
0°-40°	2154.0	73.1
0°-60°	2914.4	98.9
0°-90°	2946.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2946.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1669	
5°	1669	159
15°	1670	472
25°	1596	731
35°	1276	792
45°	750	570
55°	193	191
65°	26	29
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P245355

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1668.7
2.5°	1668.7
5°	1668.7
7.5°	1669.5
10°	1670.4
12.5°	1672.1
15°	1670.4
17.5°	1663.5
20°	1648.2
22.5°	1625.2
25°	1596.2
27.5°	1550.1
30°	1478.5
32.5°	1384.7
35°	1276.4
37.5°	1159.6
40°	1032.6
42.5°	896.1
45°	750.3
47.5°	592.6
50°	440.0
52.5°	301.8
55°	192.7
57.5°	115.1
60°	69.1
62.5°	41.8
65°	25.6
67.5°	12.8
70°	6.0
72.5°	2.6
75°	1.7
77.5°	1.7
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)