

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844343

Luminaire Tested: **LD6C30DE010B2750 EU6C30B50 6LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844343
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C30DE010B2750 EU6C30B50 6LBMH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2216.9 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844343

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B50 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P844343

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B50 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120264
5°	118115
10°	112078
15°	105103
20°	97880
25°	90193
30°	75151
35°	52963
40°	33756
45°	20126
50°	11880
55°	7560
60°	5208
65°	3697
70°	2549
75°	2012
80°	1010
85°	0



TEST NUMBER: P844343

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B50 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.6	9.0
10°-20°	518.9	23.4
20°-30°	672.4	30.3
30°-40°	499.2	22.5
40°-50°	210.7	9.5
50°-60°	74.8	3.4
60°-70°	28.9	1.3
70°-80°	10.0	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1391.9	62.8
0°-40°	1891.1	85.3
0°-60°	2176.7	98.2
0°-90°	2216.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2216.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2194	
5°	2146	201
15°	1852	519
25°	1491	672
35°	791	499
45°	260	211
55°	79	75
65°	28	29
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P844343

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B50 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2193.8
2.5°	2187.5
5°	2146.4
7.5°	2086.2
10°	2013.4
12.5°	1934.2
15°	1851.9
17.5°	1760.2
20°	1677.8
22.5°	1592.4
25°	1491.1
27.5°	1351.7
30°	1187.2
32.5°	994.0
35°	791.4
37.5°	620.5
40°	471.7
42.5°	351.3
45°	259.6
47.5°	190.0
50°	139.3
52.5°	104.5
55°	79.1
57.5°	60.1
60°	47.5
62.5°	34.9
65°	28.5
67.5°	22.1
70°	15.9
72.5°	12.6
75°	9.5
77.5°	6.3
80°	3.2
82.5°	3.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)