

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844346

Luminaire Tested: **LD6C30DE010B2750 EU6C30B50 6LBNH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844346  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C30DE010B2750 EU6C30B50 6LBNH  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1906.9 lumens  
Efficiency: N/A  
Efficacy: 55.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 34.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844346

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B50 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P844346

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B50 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134008
5°	130690
10°	120595
15°	106760
20°	92700
25°	79287
30°	65371
35°	43052
40°	23143
45°	10241
50°	4162
55°	2992
60°	1897
65°	1362
70°	1122
75°	741
80°	1105
85°	0



TEST NUMBER: P844346

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B50 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.8	11.5
10°-20°	524.2	27.5
20°-30°	600.5	31.5
30°-40°	403.5	21.2
40°-50°	115.3	6.0
50°-60°	28.2	1.5
60°-70°	10.7	0.6
70°-80°	4.2	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1344.6	70.5
0°-40°	1748.1	91.7
0°-60°	1891.6	99.2
0°-90°	1906.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1906.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2444	
5°	2375	220
15°	1881	524
25°	1311	601
35°	643	404
45°	132	115
55°	31	28
65°	10	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P844346

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B50 6LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2444.5
2.5°	2427.1
5°	2374.9
7.5°	2281.0
10°	2166.4
12.5°	2020.2
15°	1881.1
17.5°	1735.2
20°	1589.0
22.5°	1450.0
25°	1310.8
27.5°	1182.2
30°	1032.7
32.5°	834.5
35°	643.3
37.5°	469.4
40°	323.4
42.5°	212.1
45°	132.1
47.5°	80.0
50°	48.8
52.5°	38.2
55°	31.3
57.5°	24.3
60°	17.3
62.5°	13.9
65°	10.5
67.5°	7.0
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)