

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246657

Luminaire Tested: **LSR8B30D010 EC8B30940 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30940 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2537.0 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246657

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246657

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82040
5°	81453
10°	74225
15°	63622
20°	56383
25°	50315
30°	40634
35°	28192
40°	17889
45°	13288
50°	11341
55°	9946
60°	8899
65°	7953
70°	6852
75°	6303
80°	5878
85°	5166



TEST NUMBER: P246657

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.7	9.6
10°-20°	561.4	22.1
20°-30°	667.6	26.3
30°-40°	471.9	18.6
40°-50°	243.6	9.6
50°-60°	167.0	6.6
60°-70°	108.4	4.3
70°-80°	56.9	2.2
80°-90°	17.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1471.7	58.0
0°-40°	1943.6	76.6
0°-60°	2354.2	92.8
0°-90°	2537.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2537.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2660	
5°	2631	243
15°	1993	561
25°	1479	668
35°	749	472
45°	305	244
55°	185	167
65°	109	108
75°	53	57
85°	15	16
90°	0	1
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246657

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2660.5
2.5°	2660.5
5°	2631.4
7.5°	2534.6
10°	2370.5
12.5°	2174.8
15°	1992.9
17.5°	1843.3
20°	1718.2
22.5°	1600.0
25°	1478.8
27.5°	1326.7
30°	1141.2
32.5°	941.6
35°	748.9
37.5°	577.0
40°	444.4
42.5°	357.6
45°	304.7
47.5°	266.3
50°	236.4
52.5°	210.2
55°	185.0
57.5°	162.7
60°	144.3
62.5°	125.0
65°	109.0
67.5°	94.4
70°	76.0
72.5°	65.3
75°	52.9
77.5°	42.9
80°	33.1
82.5°	24.6
85°	14.6
87.5°	8.5
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246657

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)