

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246303

Luminaire Tested: **LSR8B30D010 EC8B30950 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30950 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1816.0 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246303

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246303

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51207
5°	49920
10°	48590
15°	47688
20°	46447
25°	44800
30°	41104
35°	31516
40°	14995
45°	5708
50°	2787
55°	1140
60°	284
65°	66
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246303

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.0	8.4
10°-20°	420.4	23.1
20°-30°	600.2	33.1
30°-40°	497.4	27.4
40°-50°	122.7	6.8
50°-60°	22.1	1.2
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1172.6	64.6
0°-40°	1670.0	92.0
0°-60°	1814.7	99.9
0°-90°	1816.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1816.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1661	
5°	1613	152
15°	1494	420
25°	1317	600
35°	837	497
45°	131	123
55°	21	22
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246303

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBW0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1660.6
2.5°	1646.8
5°	1612.7
7.5°	1579.5
10°	1551.8
12.5°	1525.1
15°	1493.8
17.5°	1456.9
20°	1415.4
22.5°	1368.4
25°	1316.7
27.5°	1246.6
30°	1154.4
32.5°	1024.4
35°	837.2
37.5°	604.9
40°	372.5
42.5°	216.7
45°	130.9
47.5°	86.7
50°	58.1
52.5°	37.8
55°	21.2
57.5°	10.1
60°	4.6
62.5°	1.8
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)