

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844396

Luminaire Tested: **LD6C35DE010B2750 EU6C35B35 6LBMMW**

Issue Date: 5/7/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P844396  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C35DE010B2750 EU6C35B35 6LBMMW  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2941.3 lumens  
Efficiency: N/A  
Efficacy: 70.5 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 41.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844396

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B35 6LBMMW

### Luminous Intensity Polar Plot





TEST NUMBER: P844396

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B35 6LBMMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120314
5°	118765
10°	114716
15°	109830
20°	104367
25°	97167
30°	83715
35°	63530
40°	46451
45°	35228
50°	28724
55°	25203
60°	23123
65°	21053
70°	18849
75°	17178
80°	15406
85°	12706



TEST NUMBER: P844396

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B35 6LBMMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.7	6.9
10°-20°	543.1	18.5
20°-30°	729.2	24.8
30°-40°	598.1	20.3
40°-50°	359.2	12.2
50°-60°	238.7	8.1
60°-70°	160.0	5.4
70°-80°	86.1	2.9
80°-90°	24.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1475.0	50.1
0°-40°	2073.1	70.5
0°-60°	2671.0	90.8
0°-90°	2941.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2941.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2195	
5°	2158	203
15°	1935	543
25°	1606	729
35°	949	598
45°	454	359
55°	264	239
65°	162	160
75°	81	86
85°	20	24
90°	0	



TEST NUMBER: P844396

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B35 6LBMMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2194.7
2.5°	2178.4
5°	2158.2
7.5°	2113.6
10°	2060.8
12.5°	1995.9
15°	1935.2
17.5°	1862.0
20°	1789.0
22.5°	1708.0
25°	1606.4
27.5°	1484.8
30°	1322.5
32.5°	1139.9
35°	949.3
37.5°	787.0
40°	649.1
42.5°	539.6
45°	454.4
47.5°	385.4
50°	336.8
52.5°	296.1
55°	263.7
57.5°	235.3
60°	210.9
62.5°	182.5
65°	162.3
67.5°	137.9
70°	117.6
72.5°	97.3
75°	81.1
77.5°	64.8
80°	48.8
82.5°	36.5
85°	20.2
87.5°	8.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)