

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844401

Luminaire Tested: **LD6C35DE010B2750 EU6C35B35 6LBWH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844401
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C35DE010B2750 EU6C35B35 6LBWH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3887.9 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844401

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B35 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P844401

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B35 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131453
5°	131405
10°	130392
15°	129524
20°	127545
25°	124634
30°	117353
35°	106207
40°	88680
45°	67953
50°	48118
55°	30345
60°	17115
65°	11117
70°	7261
75°	5338
80°	3220
85°	3208



TEST NUMBER: P844401

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B35 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.5	5.8
10°-20°	642.6	16.5
20°-30°	942.3	24.2
30°-40°	980.7	25.2
40°-50°	678.5	17.5
50°-60°	295.4	7.6
60°-70°	90.6	2.3
70°-80°	27.2	0.7
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1811.4	46.6
0°-40°	2792.1	71.8
0°-60°	3766.0	96.9
0°-90°	3887.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3887.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2398	
5°	2388	226
15°	2282	643
25°	2060	942
35°	1587	981
45°	876	678
55°	318	295
65°	86	91
75°	25	27
85°	5	4
90°	0	



TEST NUMBER: P844401

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B35 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2397.9
2.5°	2402.9
5°	2387.9
7.5°	2367.8
10°	2342.4
12.5°	2317.3
15°	2282.2
17.5°	2236.7
20°	2186.3
22.5°	2130.9
25°	2060.5
27.5°	1969.7
30°	1853.9
32.5°	1732.9
35°	1587.0
37.5°	1425.8
40°	1239.2
42.5°	1052.9
45°	876.5
47.5°	710.3
50°	564.2
52.5°	428.3
55°	317.5
57.5°	226.8
60°	156.1
62.5°	115.9
65°	85.7
67.5°	65.6
70°	45.3
72.5°	35.3
75°	25.2
77.5°	15.0
80°	10.2
82.5°	5.1
85°	5.1
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)