

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844405

Luminaire Tested: **LD6C35DE010B2750 EU6C35B40 6LBCSMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844405
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C35DE010B2750 EU6C35B40 6LBCSMW
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3993.7 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844405

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B40 6LBCSMW

Luminous Intensity Polar Plot





TEST NUMBER: P844405

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B40 6LBCSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89428
5°	89357
10°	89316
15°	88462
20°	87823
25°	86951
30°	85475
35°	84069
40°	81581
45°	78814
50°	74113
55°	67094
60°	58888
65°	49577
70°	38805
75°	27196
80°	15217
85°	10567



TEST NUMBER: P844405

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B40 6LBCSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.5	3.9
10°-20°	440.0	11.0
20°-30°	661.8	16.6
30°-40°	784.5	19.6
40°-50°	780.6	19.5
50°-60°	629.2	15.8
60°-70°	380.6	9.5
70°-80°	141.4	3.5
80°-90°	21.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1256.4	31.5
0°-40°	2040.8	51.1
0°-60°	3450.7	86.4
0°-90°	3993.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3993.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1631	
5°	1624	155
15°	1559	440
25°	1438	662
35°	1256	784
45°	1017	781
55°	702	629
65°	382	381
75°	128	141
85°	17	21
90°	0	



TEST NUMBER: P844405

CATALOG NUMBER: LD6C35DE010B2750 EU6C35B40 6LBSCMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1631.3
2.5°	1631.3
5°	1623.8
7.5°	1619.1
10°	1604.5
12.5°	1580.2
15°	1558.7
17.5°	1534.4
20°	1505.4
22.5°	1476.1
25°	1437.5
27.5°	1396.4
30°	1350.3
32.5°	1307.0
35°	1256.2
37.5°	1203.0
40°	1140.0
42.5°	1079.2
45°	1016.6
47.5°	946.2
50°	869.0
52.5°	788.8
55°	702.0
57.5°	624.3
60°	537.1
62.5°	459.9
65°	382.2
67.5°	309.7
70°	242.1
72.5°	181.7
75°	128.4
77.5°	82.3
80°	48.2
82.5°	29.0
85°	16.8
87.5°	7.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)