

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244738

Luminaire Tested: **LSR8B40D010 EC8B40827 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244738  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B40D010 EC8B40827 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 2700 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3628.0 lumens  
Efficiency: N/A  
Efficacy: 88.7 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244738

CATALOG NUMBER: LSR8B40D010 EC8B40827 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244738

CATALOG NUMBER: LSR8B40D010 EC8B40827 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	162927
5°	160655
10°	146994
15°	126206
20°	106276
25°	87786
30°	65862
35°	39255
40°	18698
45°	8146
50°	3675
55°	1613
60°	956
65°	525
70°	541
75°	0
80°	213
85°	885



TEST NUMBER: P244738

CATALOG NUMBER: LSR8B40D010 EC8B40827 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	479.3	13.2
10°-20°	1101.6	30.4
20°-30°	1168.8	32.2
30°-40°	666.9	18.4
40°-50°	165.3	4.6
50°-60°	32.4	0.9
60°-70°	9.7	0.3
70°-80°	2.2	0.1
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2749.6	75.8
0°-40°	3416.5	94.2
0°-60°	3614.2	99.6
0°-90°	3628.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3628.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5284	
5°	5190	479
15°	3953	1102
25°	2580	1169
35°	1043	667
45°	187	165
55°	30	32
65°	7	10
75°	0	2
85°	2	2
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244738

CATALOG NUMBER: LSR8B40D010 EC8B40827 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5283.6
2.5°	5281.1
5°	5190.1
7.5°	4990.1
10°	4694.5
12.5°	4337.6
15°	3953.3
17.5°	3587.0
20°	3238.6
22.5°	2903.5
25°	2580.1
27.5°	2232.8
30°	1849.7
32.5°	1437.8
35°	1042.8
37.5°	718.4
40°	464.5
42.5°	294.5
45°	186.8
47.5°	122.2
50°	76.6
52.5°	46.6
55°	30.0
57.5°	24.0
60°	15.5
62.5°	14.4
65°	7.2
67.5°	7.2
70°	6.0
72.5°	3.5
75°	0.0
77.5°	1.2
80°	1.2
82.5°	2.5
85°	2.5
87.5°	1.2
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244738

CATALOG NUMBER: LSR8B40D010 EC8B40827 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)