

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844446

Luminaire Tested: **LD6C40DE010B2750 EU6C40B27 6LBMLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P844446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C40DE010B2750 EU6C40B27 6LBMLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4467.4 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844446

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B27 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P844446

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B27 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94				94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82				82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76				76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71				71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67				67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63				63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59				59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306489
5°	303571
10°	287664
15°	261171
20°	230787
25°	199518
30°	155967
35°	95646
40°	49092
45°	19506
50°	6328
55°	2179
60°	1864
65°	1492
70°	914
75°	1207
80°	0
85°	0



TEST NUMBER: P844446

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B27 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.0	11.5
10°-20°	1282.3	28.7
20°-30°	1490.6	33.4
30°-40°	912.8	20.4
40°-50°	226.7	5.1
50°-60°	26.5	0.6
60°-70°	9.9	0.2
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3287.9	73.6
0°-40°	4200.6	94.0
0°-60°	4453.8	99.7
0°-90°	4467.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4467.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5591	
5°	5516	515
15°	4602	1282
25°	3298	1491
35°	1429	913
45°	252	227
55°	23	26
65°	12	10
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P844446

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B27 6LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5590.8
2.5°	5585.0
5°	5516.5
7.5°	5367.8
10°	5167.7
12.5°	4904.8
15°	4601.8
17.5°	4276.0
20°	3956.0
22.5°	3635.6
25°	3298.5
27.5°	2909.8
30°	2463.9
32.5°	1943.6
35°	1429.2
37.5°	1006.0
40°	686.0
42.5°	428.7
45°	251.6
47.5°	143.0
50°	74.2
52.5°	34.4
55°	22.8
57.5°	17.0
60°	17.0
62.5°	11.5
65°	11.5
67.5°	5.7
70°	5.7
72.5°	5.7
75°	5.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)