

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844449

Luminaire Tested: **LD6C40DE010B2750 EU6C40B27 6LBNLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P844449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C40DE010B2750 EU6C40B27 6LBNLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3970.2 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844449

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B27 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P844449

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B27 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 101 | 99 | 98 | 97 | 96 | 95 | | | |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 93 | 91 | 89 | | | |
| 3 | 105 | 99 | 94 | 91 | 103 | 97 | 93 | 90 | 95 | 91 | 89 | 93 | 90 | 87 | 90 | 88 | 86 | 85 | | | |
| 4 | 100 | 93 | 88 | 85 | 98 | 92 | 88 | 84 | 90 | 86 | 83 | 88 | 85 | 82 | 86 | 84 | 81 | 80 | | | |
| 5 | 96 | 88 | 83 | 79 | 94 | 87 | 83 | 79 | 86 | 82 | 78 | 84 | 81 | 78 | 83 | 80 | 77 | 76 | | | |
| 6 | 92 | 84 | 79 | 75 | 90 | 83 | 78 | 75 | 82 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 73 | 72 | | | |
| 7 | 88 | 80 | 74 | 71 | 87 | 79 | 74 | 71 | 78 | 73 | 70 | 77 | 73 | 70 | 76 | 72 | 69 | 68 | | | |
| 8 | 84 | 76 | 71 | 67 | 83 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 73 | 69 | 66 | 65 | | | |
| 9 | 81 | 73 | 67 | 64 | 80 | 72 | 67 | 64 | 71 | 67 | 63 | 70 | 66 | 63 | 70 | 66 | 63 | 62 | | | |
| 10 | 78 | 69 | 64 | 61 | 77 | 69 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 60 | 67 | 63 | 60 | 59 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 495552 |
| 5° | 463426 |
| 10° | 377960 |
| 15° | 278123 |
| 20° | 191706 |
| 25° | 142321 |
| 30° | 106903 |
| 35° | 66662 |
| 40° | 32353 |
| 45° | 11102 |
| 50° | 1450 |
| 55° | 1099 |
| 60° | 625 |
| 65° | 739 |
| 70° | 914 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P844449

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B27 6LBNLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 751.6 | 18.9 |
| 10°-20° | 1349.0 | 34.0 |
| 20°-30° | 1090.7 | 27.5 |
| 30°-40° | 628.3 | 15.8 |
| 40°-50° | 132.8 | 3.3 |
| 50°-60° | 11.4 | 0.3 |
| 60°-70° | 5.7 | 0.1 |
| 70°-80° | 0.7 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3191.3 | 80.4 |
| 0°-40° | 3819.6 | 96.2 |
| 0°-60° | 3963.8 | 99.8 |
| 0°-90° | 3970.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3970.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 9040 | |
| 5° | 8421 | 752 |
| 15° | 4900 | 1349 |
| 25° | 2353 | 1091 |
| 35° | 996 | 628 |
| 45° | 143 | 133 |
| 55° | 12 | 11 |
| 65° | 6 | 6 |
| 75° | 0 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P844449

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B27 6LBNLI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 9039.6 |
| 2.5° | 8931.0 |
| 5° | 8421.4 |
| 7.5° | 7688.6 |
| 10° | 6789.8 |
| 12.5° | 5868.1 |
| 15° | 4900.5 |
| 17.5° | 3967.4 |
| 20° | 3286.1 |
| 22.5° | 2765.2 |
| 25° | 2352.9 |
| 27.5° | 2003.8 |
| 30° | 1688.8 |
| 32.5° | 1339.7 |
| 35° | 996.1 |
| 37.5° | 692.6 |
| 40° | 452.1 |
| 42.5° | 274.9 |
| 45° | 143.2 |
| 47.5° | 57.2 |
| 50° | 17.0 |
| 52.5° | 17.0 |
| 55° | 11.5 |
| 57.5° | 11.5 |
| 60° | 5.7 |
| 62.5° | 5.7 |
| 65° | 5.7 |
| 67.5° | 5.7 |
| 70° | 5.7 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)