

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844469

Luminaire Tested: **LD6C40DE010B2750 EU6C40B30 6LBWH**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P844469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C40DE010B2750 EU6C40B30 6LBWH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4354.2 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844469

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P844469

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147220
5°	147171
10°	146039
15°	145063
20°	142847
25°	139587
30°	131425
35°	118949
40°	99322
45°	76109
50°	53900
55°	33987
60°	19165
65°	12440
70°	8126
75°	5973
80°	3567
85°	3585



TEST NUMBER: P844469

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.7	5.8
10°-20°	719.7	16.5
20°-30°	1055.3	24.2
30°-40°	1098.3	25.2
40°-50°	759.9	17.5
50°-60°	330.8	7.6
60°-70°	101.4	2.3
70°-80°	30.4	0.7
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2028.7	46.6
0°-40°	3127.0	71.8
0°-60°	4217.7	96.9
0°-90°	4354.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4354.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2686	
5°	2674	254
15°	2556	720
25°	2308	1055
35°	1777	1098
45°	982	760
55°	356	331
65°	96	101
75°	28	30
85°	6	5
90°	0	



TEST NUMBER: P844469

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B30 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2685.5
2.5°	2691.3
5°	2674.4
7.5°	2651.9
10°	2623.5
12.5°	2595.3
15°	2556.0
17.5°	2505.0
20°	2448.6
22.5°	2386.6
25°	2307.7
27.5°	2206.1
30°	2076.2
32.5°	1940.8
35°	1777.4
37.5°	1596.8
40°	1387.9
42.5°	1179.2
45°	981.7
47.5°	795.4
50°	632.0
52.5°	479.6
55°	355.6
57.5°	253.9
60°	174.8
62.5°	129.8
65°	95.9
67.5°	73.4
70°	50.7
72.5°	39.6
75°	28.2
77.5°	16.8
80°	11.3
82.5°	5.7
85°	5.7
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)