

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244726

Luminaire Tested: **LSR8B40D010 EC8B40927 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244726  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B40D010 EC8B40927 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3352.4 lumens  
Efficiency: N/A  
Efficacy: 82.0 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244726

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244726

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244726

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.1	6.7
10°-20°	620.6	18.5
20°-30°	924.4	27.6
30°-40°	858.5	25.6
40°-50°	405.5	12.1
50°-60°	217.9	6.5
60°-70°	87.4	2.6
70°-80°	13.7	0.4
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1768.1	52.7
0°-40°	2626.6	78.3
0°-60°	3249.9	96.9
0°-90°	3352.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3352.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2430	
5°	2372	223
15°	2197	621
25°	2023	924
35°	1427	858
45°	495	405
55°	240	218
65°	87	87
75°	11	14
85°	1	1
90°	0	



TEST NUMBER: P244726

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2429.5
2.5°	2412.9
5°	2371.6
7.5°	2319.3
10°	2270.2
12.5°	2230.2
15°	2196.8
17.5°	2162.2
20°	2124.3
22.5°	2080.9
25°	2023.0
27.5°	1941.6
30°	1829.1
32.5°	1664.3
35°	1427.0
37.5°	1124.0
40°	833.3
42.5°	620.4
45°	494.6
47.5°	413.3
50°	348.6
52.5°	290.7
55°	239.5
57.5°	195.0
60°	158.2
62.5°	123.6
65°	86.9
67.5°	51.2
70°	30.0
72.5°	17.8
75°	11.1
77.5°	6.6
80°	3.4
82.5°	2.2
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)