

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246652

Luminaire Tested: **LSR8B40D010 EC8B40935 8LBN0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246652  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B40D010 EC8B40935 8LBN0MW  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3456.0 lumens  
Efficiency: N/A  
Efficacy: 84.5 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246652

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBN0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P246652

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBN0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	111760
5°	110958
10°	101113
15°	86668
20°	76811
25°	68542
30°	55354
35°	38405
40°	24370
45°	18102
50°	15452
55°	13548
60°	12119
65°	10828
70°	9331
75°	8590
80°	7991
85°	7076



TEST NUMBER: P246652

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBN0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	330.6	9.6
10°-20°	764.7	22.1
20°-30°	909.4	26.3
30°-40°	642.9	18.6
40°-50°	331.9	9.6
50°-60°	227.5	6.6
60°-70°	147.7	4.3
70°-80°	77.5	2.2
80°-90°	23.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2004.8	58.0
0°-40°	2647.7	76.6
0°-60°	3207.1	92.8
0°-90°	3456.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3456.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3624	
5°	3585	331
15°	2715	765
25°	2014	909
35°	1020	643
45°	415	332
55°	252	228
65°	148	148
75°	72	77
85°	20	22
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246652

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBN0MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3624.3
2.5°	3624.3
5°	3584.6
7.5°	3452.8
10°	3229.2
12.5°	2962.6
15°	2714.8
17.5°	2511.0
20°	2340.7
22.5°	2179.6
25°	2014.5
27.5°	1807.3
30°	1554.6
32.5°	1282.7
35°	1020.2
37.5°	786.1
40°	605.4
42.5°	487.1
45°	415.1
47.5°	362.8
50°	322.1
52.5°	286.4
55°	252.0
57.5°	221.6
60°	196.5
62.5°	170.3
65°	148.4
67.5°	128.6
70°	103.5
72.5°	88.9
75°	72.1
77.5°	58.5
80°	45.0
82.5°	33.5
85°	20.0
87.5°	11.5
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246652

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBN0MW

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)