

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844482

Luminaire Tested: **LD6C40DE010B2750 EU6C40B35 6LBNH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844482
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C40DE010B2750 EU6C40B35 6LBNH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3177.1 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844482

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B35 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P844482

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B35 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	223266
5°	217741
10°	200915
15°	177878
20°	154451
25°	132104
30°	108915
35°	71721
40°	38558
45°	17072
50°	6917
55°	4989
60°	3169
65°	2270
70°	1859
75°	1228
80°	1831
85°	0



TEST NUMBER: P844482

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B35 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.2	11.5
10°-20°	873.4	27.5
20°-30°	1000.6	31.5
30°-40°	672.3	21.2
40°-50°	192.1	6.0
50°-60°	47.0	1.5
60°-70°	17.9	0.6
70°-80°	6.9	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2240.2	70.5
0°-40°	2912.5	91.7
0°-60°	3151.5	99.2
0°-90°	3177.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3177.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4073	
5°	3957	366
15°	3134	873
25°	2184	1001
35°	1072	672
45°	220	192
55°	52	47
65°	18	18
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P844482

CATALOG NUMBER: LD6C40DE010B2750 EU6C40B35 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4072.7
2.5°	4043.9
5°	3956.8
7.5°	3800.4
10°	3609.3
12.5°	3365.8
15°	3134.2
17.5°	2890.9
20°	2647.5
22.5°	2415.8
25°	2184.0
27.5°	1969.7
30°	1720.6
32.5°	1390.4
35°	1071.7
37.5°	782.0
40°	538.8
42.5°	353.4
45°	220.2
47.5°	133.2
50°	81.1
52.5°	63.7
55°	52.2
57.5°	40.6
60°	28.9
62.5°	23.1
65°	17.5
67.5°	11.6
70°	11.6
72.5°	5.8
75°	5.8
77.5°	5.8
80°	5.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)