

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243850

Luminaire Tested: **LSR8B40D010 EC8B40940 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243850  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B40D010 EC8B40940 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4135.0 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243850

CATALOG NUMBER: LSR8B40D010 EC8B40940 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243850

CATALOG NUMBER: LSR8B40D010 EC8B40940 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	73366
5°	75534
10°	81828
15°	89531
20°	93146
25°	92804
30°	87051
35°	72996
40°	50821
45°	29109
50°	15630
55°	6446
60°	1603
65°	416
70°	207
75°	131
80°	195
85°	0



TEST NUMBER: P243850

CATALOG NUMBER: LSR8B40D010 EC8B40940 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	238.6	5.8
10°-20°	790.4	19.1
20°-30°	1243.7	30.1
30°-40°	1183.0	28.6
40°-50°	545.4	13.2
50°-60°	123.9	3.0
60°-70°	8.2	0.2
70°-80°	1.6	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2272.7	55.0
0°-40°	3455.7	83.6
0°-60°	4125.1	99.8
0°-90°	4135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4135.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2379	
5°	2440	239
15°	2804	790
25°	2728	1244
35°	1939	1183
45°	668	545
55°	120	124
65°	6	8
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P243850

CATALOG NUMBER: LSR8B40D010 EC8B40940 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2379.2
1°	2378.0
2°	2382.5
3°	2396.1
4°	2416.5
5°	2440.2
6°	2469.7
7°	2501.3
8°	2534.1
9°	2572.6
10°	2613.3
11°	2654.1
12°	2697.0
13°	2737.8
14°	2775.1
15°	2804.5
16°	2826.0
17°	2840.7
18°	2847.5
19°	2846.4
20°	2838.5
21°	2824.9
22°	2807.9
23°	2785.3
24°	2759.3
25°	2727.6
26°	2690.3
27°	2642.7
28°	2586.2
29°	2520.6
30°	2444.8
32.5°	2217.4
35°	1939.1
37.5°	1615.5
40°	1262.5
42.5°	933.3
45°	667.5
47.5°	472.9
50°	325.8
52.5°	208.2
55°	119.9
57.5°	60.0
60°	26.0
62.5°	10.2
65°	5.7



TEST NUMBER: P243850

CATALOG NUMBER: LSR8B40D010 EC8B40940 8LBW0LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	3.4
70°	2.3
72.5°	2.3
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)