

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245267

Luminaire Tested: **LSR8B50D010 EC8B50850 8LBM0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50850 8LBM0WH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5661.0 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245267

CATALOG NUMBER: LSR8B50D010 EC8B50850 8LBM0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245267

CATALOG NUMBER: LSR8B50D010 EC8B50850 8LBM0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219138
5°	223346
10°	212944
15°	188030
20°	162941
25°	137682
30°	103466
35°	69280
40°	38797
45°	15586
50°	5397
55°	1495
60°	845
65°	737
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245267

CATALOG NUMBER: LSR8B50D010 EC8B50850 8LBM0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	675.1	11.9
10°-20°	1642.8	29.0
20°-30°	1823.0	32.2
30°-40°	1154.9	20.4
40°-50°	320.5	5.7
50°-60°	36.7	0.6
60°-70°	7.2	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4140.9	73.1
0°-40°	5295.9	93.6
0°-60°	5653.0	99.9
0°-90°	5661.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5661.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7106	
5°	7215	675
15°	5890	1643
25°	4047	1823
35°	1840	1155
45°	357	320
55°	28	37
65°	10	7
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245267

CATALOG NUMBER: LSR8B50D010 EC8B50850 8LBM0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7106.5
2.5°	7159.0
5°	7215.4
7.5°	7102.9
10°	6800.7
12.5°	6369.9
15°	5889.9
17.5°	5418.5
20°	4965.4
22.5°	4520.8
25°	4046.6
27.5°	3492.0
30°	2905.8
32.5°	2338.1
35°	1840.4
37.5°	1390.7
40°	963.8
42.5°	599.4
45°	357.4
47.5°	205.5
50°	112.5
52.5°	55.1
55°	27.8
57.5°	20.9
60°	13.7
62.5°	7.2
65°	10.1
67.5°	5.1
70°	0.0
72.5°	1.4
75°	0.0
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245267

CATALOG NUMBER: LSR8B50D010 EC8B50850 8LBM0WH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)