

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246317

Luminaire Tested: **LSR8B50D010 EC8B50930 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246317
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50930 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2893.3 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246317

CATALOG NUMBER: LSR8B50D010 EC8B50930 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246317

CATALOG NUMBER: LSR8B50D010 EC8B50930 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246317

CATALOG NUMBER: LSR8B50D010 EC8B50930 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.2	8.4
10°-20°	669.7	23.1
20°-30°	956.3	33.1
30°-40°	792.5	27.4
40°-50°	195.4	6.8
50°-60°	35.1	1.2
60°-70°	2.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1868.2	64.6
0°-40°	2660.7	92.0
0°-60°	2891.3	99.9
0°-90°	2893.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2893.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2646	
5°	2569	242
15°	2380	670
25°	2098	956
35°	1334	793
45°	209	195
55°	34	35
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246317

CATALOG NUMBER: LSR8B50D010 EC8B50930 8LBW0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2645.8
2.5°	2623.7
5°	2569.4
7.5°	2516.5
10°	2472.5
12.5°	2429.9
15°	2379.9
17.5°	2321.1
20°	2255.0
22.5°	2180.1
25°	2097.8
27.5°	1986.2
30°	1839.2
32.5°	1632.2
35°	1333.9
37.5°	963.7
40°	593.5
42.5°	345.3
45°	208.6
47.5°	138.1
50°	92.6
52.5°	60.2
55°	33.7
57.5°	16.1
60°	7.4
62.5°	2.9
65°	1.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)