

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246437

Luminaire Tested: **LSR8B50D010 EC8B50935 8LBM0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246437  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201569)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B50D010 EC8B50935 8LBM0B  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2938.0 lumens  
Efficiency: N/A  
Efficacy: 55.4 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246437

CATALOG NUMBER: LSR8B50D010 EC8B50935 8LBM0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246437

CATALOG NUMBER: LSR8B50D010 EC8B50935 8LBM0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	93	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117526
5°	113933
10°	99782
15°	88107
20°	80719
25°	74349
30°	61884
35°	41100
40°	19994
45°	7222
50°	2192
55°	151
60°	0
65°	95
70°	0
75°	0
80°	231
85°	0



TEST NUMBER: P246437

CATALOG NUMBER: LSR8B50D010 EC8B50935 8LBM0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	335.0	11.4
10°-20°	778.7	26.5
20°-30°	985.5	33.5
30°-40°	676.1	23.0
40°-50°	153.8	5.2
50°-60°	7.6	0.3
60°-70°	0.3	0.0
70°-80°	0.5	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2099.2	71.4
0°-40°	2775.3	94.5
0°-60°	2936.6	100.0
0°-90°	2938.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2938.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3811	
5°	3681	335
15°	2760	779
25°	2185	986
35°	1092	676
45°	166	154
55°	3	8
65°	1	0
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246437

CATALOG NUMBER: LSR8B50D010 EC8B50935 8LBM0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3811.3
2.5°	3811.3
5°	3680.7
7.5°	3456.1
10°	3186.7
12.5°	2949.8
15°	2759.9
17.5°	2601.0
20°	2459.8
22.5°	2326.4
25°	2185.2
27.5°	1988.5
30°	1738.0
32.5°	1423.2
35°	1091.8
37.5°	771.4
40°	496.7
42.5°	292.3
45°	165.6
47.5°	88.8
50°	45.7
52.5°	8.1
55°	2.8
57.5°	1.3
60°	0.0
62.5°	0.0
65°	1.3
67.5°	0.0
70°	0.0
72.5°	1.3
75°	0.0
77.5°	0.0
80°	1.3
82.5°	0.0
85°	0.0
87.5°	1.3
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246437

CATALOG NUMBER: LSR8B50D010 EC8B50935 8LBM0B

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)