

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246515

Luminaire Tested: **LSR8B50D010 EC8B50940 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50940 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4469.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246515

CATALOG NUMBER: LSR8B50D010 EC8B50940 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P246515

CATALOG NUMBER: LSR8B50D010 EC8B50940 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56		65	60	55		64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79832
5°	79744
10°	79326
15°	78750
20°	77881
25°	76650
30°	74400
35°	70899
40°	65666
45°	55100
50°	36431
55°	17983
60°	7136
65°	2773
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P246515

CATALOG NUMBER: LSR8B50D010 EC8B50940 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.5	5.5
10°-20°	695.3	15.6
20°-30°	1035.0	23.2
30°-40°	1172.2	26.2
40°-50°	947.7	21.2
50°-60°	328.7	7.4
60°-70°	44.9	1.0
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1974.8	44.2
0°-40°	3147.0	70.4
0°-60°	4423.4	99.0
0°-90°	4469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4469.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2589	
5°	2576	244
15°	2467	695
25°	2253	1035
35°	1883	1172
45°	1264	948
55°	334	329
65°	38	45
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P246515

CATALOG NUMBER: LSR8B50D010 EC8B50940 8LBS0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2588.9
2.5°	2585.7
5°	2576.2
7.5°	2557.2
10°	2533.4
12.5°	2501.7
15°	2466.8
17.5°	2422.4
20°	2373.3
22.5°	2316.2
25°	2252.8
27.5°	2176.7
30°	2089.5
32.5°	1991.2
35°	1883.4
37.5°	1764.5
40°	1631.3
42.5°	1468.0
45°	1263.5
47.5°	1016.2
50°	759.4
52.5°	520.0
55°	334.5
57.5°	198.2
60°	115.7
62.5°	68.2
65°	38.0
67.5°	17.4
70°	4.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)