

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246383

Luminaire Tested: **LSR8B50D010 EC8B509727 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201749)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B509727 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: 1887 (1 lamp)
Luminaire Lumens: 2203.9 lumens
Efficiency: 116.8%
Efficacy: 41.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246383

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P246383

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	139	139	139	139	136	136	136	136	130	130	130	124	124	124	119	119	119	117		
1	133	130	127	125	130	128	125	123	123	121	119	119	117	116	115	113	112	110		
2	127	122	117	114	125	120	116	113	116	113	110	113	110	108	110	107	106	104		
3	121	114	109	105	119	113	108	104	110	106	102	107	104	101	104	102	99	97		
4	116	108	102	97	114	106	101	97	104	99	95	102	98	94	100	96	93	92		
5	111	102	95	91	109	100	95	90	98	93	89	97	92	89	95	91	88	86		
6	106	96	89	85	104	95	89	85	93	88	84	92	87	83	90	86	83	81		
7	101	91	84	80	99	90	84	80	89	83	79	87	82	79	86	82	78	77		
8	96	86	80	75	95	85	79	75	84	79	75	83	78	74	82	77	74	73		
9	92	82	75	71	91	81	75	71	80	75	71	79	74	70	78	74	70	69		
10	88	78	72	67	87	77	71	67	76	71	67	76	70	67	75	70	67	65		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246383

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0B

ZONAL LUMENS:

CANDELA DISTRIBUTION:

Zone	Lumens	% Fixture	% Lamp	0°	Flux	
0°-10°	315.6	14.3	16.7	0°	3518	
10°-20°	687.9	31.2	36.5	5°	3449	316
20°-30°	736.9	33.4	39.1	15°	2452	688
30°-40°	399.4	18.1	21.2	25°	1634	737
40°-50°	62.0	2.8	3.3	35°	626	399
50°-60°	1.7	0.1	0.1	45°	57	62
60°-70°	0.4	0.0	0.0	55°	0	2
70°-80°	0.0	0.0	0.0	65°	0	0
80°-90°	0.0	0.0	0.0	75°	0	0
90°-100°	0.0	0.0	0.0	85°	0	0
100°-110°	0.0	0.0	0.0	90°	0	0
110°-120°	0.0	0.0	0.0	95°	0	0
120°-130°	0.0	0.0	0.0	105°	0	0
130°-140°	0.0	0.0	0.0	115°	0	0
140°-150°	0.0	0.0	0.0	125°	0	0
150°-160°	0.0	0.0	0.0	135°	0	0
160°-170°	0.0	0.0	0.0	145°	0	0
170°-180°	0.0	0.0	0.0	155°	0	0
0°-30°	1740.4	79.0	92.2	165°	0	0
0°-40°	2139.8	97.1	113.4	175°	0	0
0°-60°	2203.5	100.0	116.8	180°	0	0
0°-90°	2203.9	100.0	116.8			
90°-120°	0.0	0.0	0.0			
90°-150°	0.0	0.0	0.0			
90°-180°	0.0	0.0	0.0			
0°-180°	2203.9	100.0	116.8			



TEST NUMBER: P246383

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3517.9
2.5°	3515.6
5°	3449.2
7.5°	3284.6
10°	3029.1
12.5°	2731.5
15°	2451.5
17.5°	2214.6
20°	2008.1
22.5°	1822.6
25°	1633.6
27.5°	1420.1
30°	1169.2
32.5°	891.5
35°	625.5
37.5°	400.3
40°	231.0
42.5°	123.6
45°	57.0
47.5°	30.3
50°	10.4
52.5°	1.1
55°	0.0
57.5°	1.1
60°	1.1
62.5°	0.0
65°	0.0
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246383

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)