

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843899

Luminaire Tested: **LD6C08DE010B2750 EU6C08B40 6LBMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C08DE010B2750 EU6C08B40 6LBMB
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 362.8 lumens
Efficiency: N/A
Efficacy: 37.8 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843899

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B40 6LBMB

Luminous Intensity Polar Plot





TEST NUMBER: P843899

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B40 6LBMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	108	104	101		109	105	103	100		101	99	97		98	96	94		94	92	91
2	104	97	92	88		101	96	91	87		92	88	85		89	86	83		86	83	81
3	97	88	82	77		95	87	81	76		84	79	75		82	77	74		79	76	73
4	90	81	74	68		88	80	73	68		77	72	67		75	70	66		73	69	65
5	85	74	67	61		83	73	66	61		71	65	61		69	64	60		68	63	59
6	79	68	61	56		78	68	61	56		66	60	55		64	59	55		63	58	54
7	75	63	56	51		73	63	56	51		61	55	50		60	54	50		59	54	50
8	70	59	52	47		69	58	51	47		57	51	46		56	50	46		55	50	46
9	66	55	48	43		65	54	48	43		53	47	43		52	47	43		51	46	43
10	63	51	45	40		62	51	44	40		50	44	40		49	44	40		48	43	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14834
5°	14649
10°	14145
15°	13547
20°	12869
25°	11983
30°	10324
35°	7837
40°	5732
45°	4349
50°	3548
55°	3106
60°	2851
65°	2594
70°	2324
75°	2118
80°	1894
85°	1572



TEST NUMBER: P843899

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B40 6LBMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.0	6.9
10°-20°	67.0	18.5
20°-30°	89.9	24.8
30°-40°	73.8	20.3
40°-50°	44.3	12.2
50°-60°	29.4	8.1
60°-70°	19.7	5.4
70°-80°	10.6	2.9
80°-90°	3.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.9	50.1
0°-40°	255.7	70.5
0°-60°	329.4	90.8
0°-90°	362.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	362.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	271	
5°	266	25
15°	239	67
25°	198	90
35°	117	74
45°	56	44
55°	32	29
65°	20	20
75°	10	11
85°	2	3
90°	0	



TEST NUMBER: P843899

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B40 6LBMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	270.6
2.5°	268.6
5°	266.2
7.5°	260.7
10°	254.1
12.5°	246.1
15°	238.7
17.5°	229.6
20°	220.6
22.5°	210.7
25°	198.1
27.5°	183.1
30°	163.1
32.5°	140.6
35°	117.1
37.5°	97.1
40°	80.1
42.5°	66.5
45°	56.1
47.5°	47.5
50°	41.6
52.5°	36.5
55°	32.5
57.5°	29.0
60°	26.0
62.5°	22.5
65°	20.0
67.5°	17.0
70°	14.5
72.5°	12.1
75°	10.0
77.5°	8.0
80°	6.0
82.5°	4.5
85°	2.5
87.5°	1.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)