

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244013

Luminaire Tested: **LSR8B50D010 EC8B509730 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B509730 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4207.0 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244013

CATALOG NUMBER: LSR8B50D010 EC8B509730 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P244013

CATALOG NUMBER: LSR8B50D010 EC8B509730 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	114	111	109	107	111	109	107	105	105	104	102	101	100	99	98	97	96	94	94	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89	89	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83	83	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78	78	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74	74	74
6	90	82	77	73	89	81	76	73	80	75	72	79	75	72	77	74	71	70	70	70
7	86	78	72	69	85	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62	62	62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	60	59	59	59
10	76	67	62	58	75	67	61	58	66	61	58	65	61	58	64	60	58	56	56	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244013

CATALOG NUMBER: LSR8B50D010 EC8B509730 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	642.2	15.3
10°-20°	1347.4	32.0
20°-30°	1318.4	31.3
30°-40°	729.4	17.3
40°-50°	141.2	3.4
50°-60°	21.7	0.5
60°-70°	5.3	0.1
70°-80°	1.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3308.0	78.6
0°-40°	4037.4	96.0
0°-60°	4200.3	99.8
0°-90°	4207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7339	
5°	6997	642
15°	4852	1347
25°	2879	1318
35°	1148	729
45°	161	141
55°	20	22
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244013

CATALOG NUMBER: LSR8B50D010 EC8B509730 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7339.0
2.5°	7238.1
5°	6996.9
7.5°	6658.6
10°	6157.8
12.5°	5524.6
15°	4852.1
17.5°	4221.5
20°	3697.1
22.5°	3263.1
25°	2879.0
27.5°	2517.1
30°	2131.7
32.5°	1679.4
35°	1148.4
37.5°	690.9
40°	405.1
42.5°	253.0
45°	161.3
47.5°	100.9
50°	59.0
52.5°	32.8
55°	19.7
57.5°	11.8
60°	9.2
62.5°	6.6
65°	5.2
67.5°	3.9
70°	2.6
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)