

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251438

Luminaire Tested: **LSR8B60D010 EC8B60827 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60827 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5388.0 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251438

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251438

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 109 | 106 | 104 | 101 | 102 | 100 | 98 | 98 | 97 | 95 | 95 | 94 | 92 | 90 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | 91 | 88 | 85 | 88 | 86 | 83 | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 78 | 76 | 74 |
| 4 | 93 | 84 | 77 | 72 | 91 | 83 | 76 | 72 | 80 | 75 | 71 | 78 | 74 | 70 | 76 | 72 | 69 | 67 |
| 5 | 87 | 78 | 71 | 66 | 85 | 77 | 70 | 65 | 75 | 69 | 65 | 73 | 68 | 64 | 71 | 67 | 64 | 62 |
| 6 | 82 | 72 | 65 | 60 | 81 | 71 | 65 | 60 | 70 | 64 | 60 | 68 | 63 | 59 | 67 | 62 | 59 | 57 |
| 7 | 78 | 67 | 60 | 56 | 76 | 67 | 60 | 55 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 54 | 53 |
| 8 | 74 | 63 | 56 | 52 | 72 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 49 |
| 9 | 70 | 59 | 53 | 48 | 69 | 59 | 52 | 48 | 58 | 52 | 48 | 57 | 51 | 48 | 56 | 51 | 47 | 46 |
| 10 | 66 | 56 | 49 | 45 | 65 | 55 | 49 | 45 | 54 | 49 | 45 | 54 | 48 | 45 | 53 | 48 | 45 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 174234 |
| 5° | 172987 |
| 10° | 157640 |
| 15° | 135119 |
| 20° | 119750 |
| 25° | 106856 |
| 30° | 86300 |
| 35° | 59877 |
| 40° | 37992 |
| 45° | 28219 |
| 50° | 24087 |
| 55° | 21118 |
| 60° | 18896 |
| 65° | 16884 |
| 70° | 14552 |
| 75° | 13380 |
| 80° | 12466 |
| 85° | 11003 |



TEST NUMBER: P251438

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBN0MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 515.5 | 9.6 |
| 10°-20° | 1192.2 | 22.1 |
| 20°-30° | 1417.8 | 26.3 |
| 30°-40° | 1002.3 | 18.6 |
| 40°-50° | 517.4 | 9.6 |
| 50°-60° | 354.7 | 6.6 |
| 60°-70° | 230.2 | 4.3 |
| 70°-80° | 120.7 | 2.2 |
| 80°-90° | 37.1 | 0.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3125.5 | 58.0 |
| 0°-40° | 4127.8 | 76.6 |
| 0°-60° | 4999.9 | 92.8 |
| 0°-90° | 5388.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5388.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|------|------|------|
| 0° | 5650 | |
| 5° | 5588 | 515 |
| 15° | 4232 | 1192 |
| 25° | 3141 | 1418 |
| 35° | 1591 | 1002 |
| 45° | 647 | 517 |
| 55° | 393 | 355 |
| 65° | 231 | 230 |
| 75° | 112 | 121 |
| 85° | 31 | 35 |
| 90° | 0 | 2 |
| 95° | 0 | 0 |
| 105° | 0 | 0 |
| 115° | 0 | 0 |
| 125° | 0 | 0 |
| 135° | 0 | 0 |
| 145° | 0 | 0 |
| 155° | 0 | 0 |
| 165° | 0 | 0 |
| 175° | 0 | 0 |
| 180° | 0 | 0 |



TEST NUMBER: P251438

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBN0MW

CANDELA DISTRIBUTION (FULL):

| 0° | |
|--------|--------|
| 0° | 5650.3 |
| 2.5° | 5650.3 |
| 5° | 5588.5 |
| 7.5° | 5383.0 |
| 10° | 5034.5 |
| 12.5° | 4618.7 |
| 15° | 4232.5 |
| 17.5° | 3914.7 |
| 20° | 3649.2 |
| 22.5° | 3398.0 |
| 25° | 3140.6 |
| 27.5° | 2817.7 |
| 30° | 2423.7 |
| 32.5° | 1999.7 |
| 35° | 1590.6 |
| 37.5° | 1225.5 |
| 40° | 943.8 |
| 42.5° | 759.5 |
| 45° | 647.1 |
| 47.5° | 565.6 |
| 50° | 502.1 |
| 52.5° | 446.5 |
| 55° | 392.8 |
| 57.5° | 345.5 |
| 60° | 306.4 |
| 62.5° | 265.5 |
| 65° | 231.4 |
| 67.5° | 200.5 |
| 70° | 161.4 |
| 72.5° | 138.6 |
| 75° | 112.3 |
| 77.5° | 91.2 |
| 80° | 70.2 |
| 82.5° | 52.3 |
| 85° | 31.1 |
| 87.5° | 18.0 |
| 90° | 0.0 |
| 92.5° | 0.0 |
| 95° | 0.0 |
| 97.5° | 0.0 |
| 100° | 0.0 |
| 102.5° | 0.0 |
| 105° | 0.0 |
| 107.5° | 0.0 |
| 110° | 0.0 |



TEST NUMBER: P251438

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBN0MW

CANDELA DISTRIBUTION (continued):

| | 0° |
|--------|-----|
| 112.5° | 0.0 |
| 115° | 0.0 |
| 117.5° | 0.0 |
| 120° | 0.0 |
| 122.5° | 0.0 |
| 125° | 0.0 |
| 127.5° | 0.0 |
| 130° | 0.0 |
| 132.5° | 0.0 |
| 135° | 0.0 |
| 137.5° | 0.0 |
| 140° | 0.0 |
| 142.5° | 0.0 |
| 145° | 0.0 |
| 147.5° | 0.0 |
| 150° | 0.0 |
| 152.5° | 0.0 |
| 155° | 0.0 |
| 157.5° | 0.0 |
| 160° | 0.0 |
| 162.5° | 0.0 |
| 165° | 0.0 |
| 167.5° | 0.0 |
| 170° | 0.0 |
| 172.5° | 0.0 |
| 175° | 0.0 |
| 177.5° | 0.0 |
| 180° | 0.0 |

(END OF REPORT)