

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251104

Luminaire Tested: **LSR8B60D010 EC8B60827 8LBW0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251104  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P200903)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60827 8LBW0WH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 2700 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6041.0 lumens  
Efficiency: N/A  
Efficacy: 101.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.11  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251104

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBW0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251104

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBW0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61	69	64	61	68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52	61	55	51	59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	122032
5°	125773
10°	134059
15°	138193
20°	138185
25°	133963
30°	119898
35°	95500
40°	69776
45°	44569
50°	24102
55°	12392
60°	5384
65°	1109
70°	766
75°	0
80°	249
85°	0



TEST NUMBER: P251104

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBW0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	395.4	6.5
10°-20°	1216.9	20.1
20°-30°	1785.3	29.6
30°-40°	1577.2	26.1
40°-50°	807.9	13.4
50°-60°	225.9	3.7
60°-70°	28.9	0.5
70°-80°	2.9	0.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3397.7	56.2
0°-40°	4974.9	82.4
0°-60°	6008.6	99.5
0°-90°	6041.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6041.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3957	
5°	4063	395
15°	4329	1217
25°	3937	1785
35°	2537	1577
45°	1022	808
55°	230	226
65°	15	29
75°	0	3
85°	0	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251104

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBW0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3957.4
2.5°	3972.6
5°	4063.2
7.5°	4187.4
10°	4281.4
12.5°	4327.2
15°	4328.8
17.5°	4285.3
20°	4211.0
22.5°	4093.6
25°	3937.3
27.5°	3704.2
30°	3367.3
32.5°	2968.1
35°	2536.9
37.5°	2116.6
40°	1733.4
42.5°	1371.7
45°	1022.0
47.5°	729.4
50°	502.4
52.5°	351.1
55°	230.5
57.5°	146.4
60°	87.3
62.5°	45.3
65°	15.2
67.5°	9.9
70°	8.5
72.5°	4.9
75°	0.0
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251104

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBW0WH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)