

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843920

Luminaire Tested: **LD6C08DE010B2750 EU6C08B50 6LBMMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843920
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C08DE010B2750 EU6C08B50 6LBMMW
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 715.0 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843920

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B50 6LBMMW

Luminous Intensity Polar Plot





TEST NUMBER: P843920

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B50 6LBMMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	108	104	101		109	105	103	100		101	99	97		98	96	94		94	92	91
2	104	97	92	88		101	96	91	87		92	88	85		89	86	83		86	83	81
3	97	88	82	77		95	87	81	76		84	79	75		82	77	74		79	76	73
4	90	81	74	68		88	80	73	68		77	72	67		75	70	66		73	69	65
5	85	74	67	61		83	73	66	61		71	65	61		69	64	60		68	63	59
6	79	68	61	56		78	68	61	56		66	60	55		64	59	55		63	58	54
7	75	63	56	51		73	63	56	51		61	55	50		60	54	50		59	54	50
8	70	59	52	47		69	58	51	47		57	51	46		56	50	46		55	50	46
9	66	55	48	43		65	54	48	43		53	47	43		52	47	43		51	46	43
10	63	51	45	40		62	51	44	40		50	44	40		49	44	40		48	43	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29247
5°	28869
10°	27883
15°	26691
20°	25371
25°	23620
30°	20345
35°	15446
40°	11293
45°	8559
50°	6985
55°	6126
60°	5625
65°	5111
70°	4584
75°	4173
80°	3725
85°	3145



TEST NUMBER: P843920

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B50 6LBMMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	6.9
10°-20°	132.0	18.5
20°-30°	177.2	24.8
30°-40°	145.4	20.3
40°-50°	87.3	12.2
50°-60°	58.0	8.1
60°-70°	38.9	5.4
70°-80°	20.9	2.9
80°-90°	5.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.5	50.1
0°-40°	503.9	70.5
0°-60°	649.2	90.8
0°-90°	715.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	715.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	534	
5°	525	49
15°	470	132
25°	390	177
35°	231	145
45°	110	87
55°	64	58
65°	39	39
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P843920

CATALOG NUMBER: LD6C08DE010B2750 EU6C08B50 6LBMMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	533.5
2.5°	529.6
5°	524.6
7.5°	513.8
10°	500.9
12.5°	485.1
15°	470.3
17.5°	452.7
20°	434.9
22.5°	415.1
25°	390.5
27.5°	360.9
30°	321.4
32.5°	277.1
35°	230.8
37.5°	191.3
40°	157.8
42.5°	131.1
45°	110.4
47.5°	93.7
50°	81.9
52.5°	72.0
55°	64.1
57.5°	57.2
60°	51.3
62.5°	44.4
65°	39.4
67.5°	33.5
70°	28.6
72.5°	23.7
75°	19.7
77.5°	15.8
80°	11.8
82.5°	8.9
85°	5.0
87.5°	2.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)