

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251158

Luminaire Tested: **LSR8B60D010 EC8B60840 8LBM0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251158  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60840 8LBM0WH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6290.0 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251158

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBM0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251158

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBM0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	243487
5°	248162
10°	236606
15°	208921
20°	181049
25°	152979
30°	114963
35°	76979
40°	43108
45°	17317
50°	5997
55°	1661
60°	937
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251158

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBM0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	750.1	11.9
10°-20°	1825.4	29.0
20°-30°	2025.6	32.2
30°-40°	1283.3	20.4
40°-50°	356.1	5.7
50°-60°	40.8	0.6
60°-70°	8.0	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4601.0	73.1
0°-40°	5884.3	93.6
0°-60°	6281.2	99.9
0°-90°	6290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6290.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7896	
5°	8017	750
15°	6544	1825
25°	4496	2026
35°	2045	1283
45°	397	356
55°	31	41
65°	11	8
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251158

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBM0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7896.1
2.5°	7954.5
5°	8017.1
7.5°	7892.1
10°	7556.4
12.5°	7077.6
15°	6544.3
17.5°	6020.6
20°	5517.2
22.5°	5023.1
25°	4496.2
27.5°	3880.0
30°	3228.7
32.5°	2597.9
35°	2044.9
37.5°	1545.2
40°	1070.9
42.5°	666.0
45°	397.1
47.5°	228.3
50°	125.0
52.5°	61.2
55°	30.9
57.5°	23.3
60°	15.2
62.5°	8.0
65°	11.2
67.5°	5.6
70°	0.0
72.5°	1.6
75°	0.0
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251158

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBM0WH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)