

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251040

Luminaire Tested: **LSR8B60D010 EC8B60850 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251040  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60850 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5552.0 lumens  
Efficiency: N/A  
Efficacy: 93.3 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251040

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P251040

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	59		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	249327
5°	245853
10°	224952
15°	193134
20°	162636
25°	134341
30°	100788
35°	60073
40°	28613
45°	12468
50°	5627
55°	2468
60°	1468
65°	803
70°	829
75°	0
80°	320
85°	1344



TEST NUMBER: P251040

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	733.5	13.2
10°-20°	1685.8	30.4
20°-30°	1788.6	32.2
30°-40°	1020.6	18.4
40°-50°	253.0	4.6
50°-60°	49.6	0.9
60°-70°	14.9	0.3
70°-80°	3.3	0.1
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4207.8	75.8
0°-40°	5228.4	94.2
0°-60°	5531.0	99.6
0°-90°	5552.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5552.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8086	
5°	7942	733
15°	6050	1686
25°	3948	1789
35°	1596	1021
45°	286	253
55°	46	50
65°	11	15
75°	0	3
85°	4	3
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251040

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8085.5
2.5°	8081.8
5°	7942.5
7.5°	7636.4
10°	7184.2
12.5°	6638.0
15°	6049.8
17.5°	5489.3
20°	4956.1
22.5°	4443.2
25°	3948.4
27.5°	3417.0
30°	2830.6
32.5°	2200.3
35°	1595.8
37.5°	1099.4
40°	710.8
42.5°	450.7
45°	285.9
47.5°	187.0
50°	117.3
52.5°	71.3
55°	45.9
57.5°	36.8
60°	23.8
62.5°	22.0
65°	11.0
67.5°	11.0
70°	9.2
72.5°	5.4
75°	0.0
77.5°	1.8
80°	1.8
82.5°	3.8
85°	3.8
87.5°	1.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251040

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)