

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844062

Luminaire Tested: **LD6C15DE010B35 EU6C15B35 6LBWLI**

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P844062  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C15DE010B35 EU6C15B35 6LBWLI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1568.5 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844062

CATALOG NUMBER: LD6C15DE010B35 EU6C15B35 6LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P844062

CATALOG NUMBER: LD6C15DE010B35 EU6C15B35 6LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	53718
5°	54215
10°	55733
15°	57123
20°	57994
25°	56798
30°	53242
35°	47609
40°	38565
45°	25507
50°	12887
55°	5438
60°	1754
65°	687
70°	577
75°	381
80°	0
85°	0



TEST NUMBER: P844062

CATALOG NUMBER: LD6C15DE010B35 EU6C15B35 6LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.5	6.0
10°-20°	284.1	18.1
20°-30°	428.3	27.3
30°-40°	438.4	27.9
40°-50°	255.4	16.3
50°-60°	58.7	3.7
60°-70°	7.2	0.5
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	806.9	51.4
0°-40°	1245.3	79.4
0°-60°	1559.4	99.4
0°-90°	1568.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1568.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	980	
5°	985	95
15°	1006	284
25°	939	428
35°	711	438
45°	329	255
55°	57	59
65°	5	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P844062

CATALOG NUMBER: LD6C15DE010B35 EU6C15B35 6LBWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	979.9
2.5°	978.1
5°	985.2
7.5°	992.3
10°	1001.2
12.5°	1003.0
15°	1006.5
17.5°	1003.0
20°	994.1
22.5°	965.6
25°	939.0
27.5°	896.2
30°	841.1
32.5°	784.2
35°	711.4
37.5°	629.5
40°	538.9
42.5°	437.4
45°	329.0
47.5°	229.4
50°	151.1
52.5°	96.0
55°	56.9
57.5°	30.2
60°	16.0
62.5°	8.9
65°	5.3
67.5°	5.3
70°	3.6
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)