

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250998

Luminaire Tested: **LSR8B60D010 EC8B60935 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60935 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5831.0 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250998

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P250998

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104347
5°	104000
10°	103211
15°	102483
20°	101790
25°	100449
30°	97345
35°	91848
40°	83475
45°	68684
50°	45780
55°	23849
60°	11243
65°	5896
70°	2948
75°	2049
80°	1527
85°	1203



TEST NUMBER: P250998

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.7	5.5
10°-20°	906.1	15.5
20°-30°	1355.4	23.2
30°-40°	1516.0	26.0
40°-50°	1189.4	20.4
50°-60°	434.0	7.4
60°-70°	88.5	1.5
70°-80°	19.0	0.3
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2580.2	44.2
0°-40°	4096.2	70.2
0°-60°	5719.6	98.1
0°-90°	5831.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5831.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3384	
5°	3360	319
15°	3210	906
25°	2952	1355
35°	2440	1516
45°	1575	1189
55°	444	434
65°	81	88
75°	17	19
85°	3	4
90°	0	



TEST NUMBER: P250998

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3383.9
2.5°	3378.7
5°	3359.8
7.5°	3332.3
10°	3296.2
12.5°	3254.9
15°	3210.2
17.5°	3160.4
20°	3101.9
22.5°	3033.1
25°	2952.3
27.5°	2852.6
30°	2733.9
32.5°	2594.7
35°	2439.9
37.5°	2266.2
40°	2073.7
42.5°	1845.0
45°	1575.0
47.5°	1270.7
50°	954.3
52.5°	668.9
55°	443.6
57.5°	283.7
60°	182.3
62.5°	120.4
65°	80.8
67.5°	51.6
70°	32.7
72.5°	22.4
75°	17.2
77.5°	12.0
80°	8.6
82.5°	5.2
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)