

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250856

Luminaire Tested: **LSR8B60D010 EC8B60940 8LBM0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250856  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60940 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5763.0 lumens  
Efficiency: N/A  
Efficacy: 96.9 lumens/watt  
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250856

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P250856

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	310013
5°	296686
10°	264129
15°	212187
20°	166190
25°	134184
30°	103975
35°	59222
40°	22337
45°	9633
50°	3876
55°	1446
60°	777
65°	525
70°	325
75°	214
80°	0
85°	0



TEST NUMBER: P250856

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	879.7	15.3
10°-20°	1845.7	32.0
20°-30°	1806.1	31.3
30°-40°	999.2	17.3
40°-50°	193.4	3.4
50°-60°	29.7	0.5
60°-70°	7.3	0.1
70°-80°	1.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4531.5	78.6
0°-40°	5530.7	96.0
0°-60°	5753.8	99.8
0°-90°	5763.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5763.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10054	
5°	9585	880
15°	6647	1846
25°	3944	1806
35°	1573	999
45°	221	193
55°	27	30
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P250856

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10053.5
2.5°	9915.2
5°	9584.7
7.5°	9121.4
10°	8435.4
12.5°	7567.9
15°	6646.6
17.5°	5782.8
20°	5064.4
22.5°	4470.0
25°	3943.8
27.5°	3448.1
30°	2920.1
32.5°	2300.6
35°	1573.2
37.5°	946.4
40°	554.9
42.5°	346.6
45°	220.9
47.5°	138.3
50°	80.8
52.5°	44.9
55°	26.9
57.5°	16.2
60°	12.6
62.5°	9.0
65°	7.2
67.5°	5.4
70°	3.6
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)