

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844141

Luminaire Tested: **LD6C20DE010B35 EU6C20B35 6LBMMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C20DE010B35 EU6C20B35 6LBMMW
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1573.7 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844141

CATALOG NUMBER: LD6C20DE010B35 EU6C20B35 6LBMMW

Luminous Intensity Polar Plot





TEST NUMBER: P844141

CATALOG NUMBER: LD6C20DE010B35 EU6C20B35 6LBMMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64375
5°	63543
10°	61383
15°	58763
20°	55847
25°	51989
30°	44792
35°	33997
40°	24854
45°	18847
50°	15368
55°	13486
60°	12367
65°	11259
70°	10082
75°	9193
80°	8208
85°	6793



TEST NUMBER: P844141

CATALOG NUMBER: LD6C20DE010B35 EU6C20B35 6LBMMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.5	6.9
10°-20°	290.6	18.5
20°-30°	390.1	24.8
30°-40°	320.0	20.3
40°-50°	192.2	12.2
50°-60°	127.7	8.1
60°-70°	85.6	5.4
70°-80°	46.0	2.9
80°-90°	13.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.2	50.1
0°-40°	1109.2	70.5
0°-60°	1429.1	90.8
0°-90°	1573.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1573.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1174	
5°	1155	108
15°	1035	291
25°	860	390
35°	508	320
45°	243	192
55°	141	128
65°	87	86
75°	43	46
85°	11	13
90°	0	



TEST NUMBER: P844141

CATALOG NUMBER: LD6C20DE010B35 EU6C20B35 6LBMWW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1174.3
2.5°	1165.6
5°	1154.7
7.5°	1130.9
10°	1102.7
12.5°	1067.9
15°	1035.4
17.5°	996.3
20°	957.3
22.5°	913.8
25°	859.5
27.5°	794.4
30°	707.6
32.5°	609.9
35°	508.0
37.5°	421.0
40°	347.3
42.5°	288.7
45°	243.1
47.5°	206.2
50°	180.2
52.5°	158.4
55°	141.1
57.5°	125.9
60°	112.8
62.5°	97.7
65°	86.8
67.5°	73.8
70°	62.9
72.5°	52.0
75°	43.4
77.5°	34.7
80°	26.0
82.5°	19.6
85°	10.8
87.5°	4.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)