

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844218

Luminaire Tested: **LD6C25DE010B35 EU6C25B35 6LBCSMW**

Issue Date: 5/7/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P844218  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C25DE010B35 EU6C25B35 6LBCSMW  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2827.0 lumens  
Efficiency: N/A  
Efficacy: 94.9 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 29.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844218

CATALOG NUMBER: LD6C25DE010B35 EU6C25B35 6LBCSMW

### Luminous Intensity Polar Plot





TEST NUMBER: P844218

CATALOG NUMBER: LD6C25DE010B35 EU6C25B35 6LBSCMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |     |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    | 100 |
| 1   | 110 | 106 | 102 | 99  | 108 | 104 | 100 | 97  | 100 | 97  | 94  | 96  | 93  | 91  | 92  | 90  | 89  | 87  |    |    |    | 87  |
| 2   | 101 | 94  | 87  | 82  | 99  | 92  | 86  | 81  | 88  | 84  | 79  | 85  | 81  | 78  | 82  | 79  | 76  | 74  |    |    |    | 74  |
| 3   | 93  | 83  | 75  | 70  | 90  | 81  | 74  | 69  | 79  | 73  | 68  | 76  | 71  | 67  | 73  | 69  | 65  | 63  |    |    |    | 63  |
| 4   | 85  | 74  | 66  | 60  | 83  | 73  | 65  | 59  | 70  | 64  | 58  | 68  | 62  | 58  | 66  | 61  | 57  | 55  |    |    |    | 55  |
| 5   | 79  | 66  | 58  | 52  | 77  | 65  | 57  | 51  | 63  | 56  | 51  | 61  | 55  | 50  | 60  | 54  | 50  | 48  |    |    |    | 48  |
| 6   | 73  | 60  | 52  | 45  | 71  | 59  | 51  | 45  | 57  | 50  | 45  | 56  | 49  | 44  | 54  | 49  | 44  | 42  |    |    |    | 42  |
| 7   | 68  | 55  | 46  | 40  | 66  | 54  | 46  | 40  | 52  | 45  | 40  | 51  | 44  | 40  | 50  | 44  | 39  | 37  |    |    |    | 37  |
| 8   | 63  | 50  | 42  | 36  | 61  | 49  | 41  | 36  | 48  | 41  | 36  | 47  | 40  | 36  | 46  | 40  | 35  | 33  |    |    |    | 33  |
| 9   | 59  | 46  | 38  | 33  | 57  | 45  | 38  | 32  | 44  | 37  | 32  | 43  | 37  | 32  | 42  | 36  | 32  | 30  |    |    |    | 30  |
| 10  | 55  | 42  | 35  | 30  | 54  | 42  | 34  | 30  | 41  | 34  | 29  | 40  | 34  | 29  | 39  | 33  | 29  | 27  |    |    |    | 27  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 63306 |
| 5°  | 63251 |
| 10° | 63225 |
| 15° | 62622 |
| 20° | 62171 |
| 25° | 61546 |
| 30° | 60503 |
| 35° | 59515 |
| 40° | 57751 |
| 45° | 55789 |
| 50° | 52459 |
| 55° | 47492 |
| 60° | 41685 |
| 65° | 35101 |
| 70° | 27457 |
| 75° | 19253 |
| 80° | 10797 |
| 85° | 7422  |



TEST NUMBER: P844218

CATALOG NUMBER: LD6C25DE010B35 EU6C25B35 6LBSCMW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 109.4  | 3.9       |
| 10°-20°   | 311.5  | 11.0      |
| 20°-30°   | 468.5  | 16.6      |
| 30°-40°   | 555.3  | 19.6      |
| 40°-50°   | 552.6  | 19.5      |
| 50°-60°   | 445.4  | 15.8      |
| 60°-70°   | 269.4  | 9.5       |
| 70°-80°   | 100.1  | 3.5       |
| 80°-90°   | 14.8   | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 889.4  | 31.5      |
| 0°-40°    | 1444.7 | 51.1      |
| 0°-60°    | 2442.7 | 86.4      |
| 0°-90°    | 2827.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2827.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1155 |      |
| 5°  | 1149 | 109  |
| 15° | 1103 | 311  |
| 25° | 1018 | 468  |
| 35° | 889  | 555  |
| 45° | 720  | 553  |
| 55° | 497  | 445  |
| 65° | 271  | 269  |
| 75° | 91   | 100  |
| 85° | 12   | 15   |
| 90° | 0    |      |



TEST NUMBER: P844218

CATALOG NUMBER: LD6C25DE010B35 EU6C25B35 6LBSCMW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1154.8 |
| 2.5°  | 1154.8 |
| 5°    | 1149.4 |
| 7.5°  | 1146.2 |
| 10°   | 1135.8 |
| 12.5° | 1118.6 |
| 15°   | 1103.4 |
| 17.5° | 1086.2 |
| 20°   | 1065.7 |
| 22.5° | 1044.9 |
| 25°   | 1017.5 |
| 27.5° | 988.5  |
| 30°   | 955.8  |
| 32.5° | 925.2  |
| 35°   | 889.3  |
| 37.5° | 851.5  |
| 40°   | 807.0  |
| 42.5° | 763.9  |
| 45°   | 719.6  |
| 47.5° | 669.8  |
| 50°   | 615.1  |
| 52.5° | 558.4  |
| 55°   | 496.9  |
| 57.5° | 442.0  |
| 60°   | 380.2  |
| 62.5° | 325.5  |
| 65°   | 270.6  |
| 67.5° | 219.2  |
| 70°   | 171.3  |
| 72.5° | 128.6  |
| 75°   | 90.9   |
| 77.5° | 58.2   |
| 80°   | 34.2   |
| 82.5° | 20.5   |
| 85°   | 11.8   |
| 87.5° | 5.1    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)