

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251122

Luminaire Tested: **LSR8B60D010 EC8B60950 8LBW0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P200903)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60950 8LBW0WH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5939.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.11
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251122

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBW0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251122

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBW0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78	75	72	70
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61		69	64	61		68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52		61	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119972
5°	123649
10°	131795
15°	135859
20°	135852
25°	131701
30°	117876
35°	93885
40°	68597
45°	43814
50°	23699
55°	12182
60°	5292
65°	1087
70°	748
75°	0
80°	249
85°	0



TEST NUMBER: P251122

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBW0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.8	6.5
10°-20°	1196.4	20.1
20°-30°	1755.2	29.6
30°-40°	1550.5	26.1
40°-50°	794.2	13.4
50°-60°	222.1	3.7
60°-70°	28.4	0.5
70°-80°	2.9	0.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3340.3	56.2
0°-40°	4890.9	82.4
0°-60°	5907.1	99.5
0°-90°	5939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5939.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3891	
5°	3995	389
15°	4256	1196
25°	3871	1755
35°	2494	1551
45°	1005	794
55°	227	222
65°	15	28
75°	0	3
85°	0	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251122

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBW0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3890.6
2.5°	3905.5
5°	3994.6
7.5°	4116.7
10°	4209.1
12.5°	4254.2
15°	4255.7
17.5°	4212.9
20°	4139.9
22.5°	4024.4
25°	3870.8
27.5°	3641.6
30°	3310.5
32.5°	2917.9
35°	2494.0
37.5°	2080.9
40°	1704.1
42.5°	1348.5
45°	1004.7
47.5°	717.1
50°	494.0
52.5°	345.2
55°	226.6
57.5°	143.9
60°	85.8
62.5°	44.6
65°	14.9
67.5°	9.7
70°	8.3
72.5°	4.9
75°	0.0
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251122

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBW0WH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)