

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246414

Luminaire Tested: **LSR8B10D010 EC8B10850 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201569)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10850 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 726.0 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246414

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P246414

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29042
5°	28153
10°	24658
15°	21772
20°	19945
25°	18373
30°	15293
35°	10156
40°	4939
45°	1784
50°	542
55°	38
60°	0
65°	22
70°	0
75°	0
80°	53
85°	0



TEST NUMBER: P246414

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.8	11.4
10°-20°	192.4	26.5
20°-30°	243.5	33.5
30°-40°	167.1	23.0
40°-50°	38.0	5.2
50°-60°	1.9	0.3
60°-70°	0.1	0.0
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.7	71.5
0°-40°	685.8	94.5
0°-60°	725.6	100.0
0°-90°	726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	726.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	942	
5°	910	83
15°	682	192
25°	540	244
35°	270	167
45°	41	38
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246414

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBM0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	941.8
2.5°	941.8
5°	909.5
7.5°	854.0
10°	787.5
12.5°	728.9
15°	682.0
17.5°	642.7
20°	607.8
22.5°	574.9
25°	540.0
27.5°	491.4
30°	429.5
32.5°	351.7
35°	269.8
37.5°	190.6
40°	122.7
42.5°	72.2
45°	40.9
47.5°	21.9
50°	11.3
52.5°	2.0
55°	0.7
57.5°	0.3
60°	0.0
62.5°	0.0
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.3
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246414

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)