

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844231

Luminaire Tested: **LD6C25DE010B35 EU6C25B35 6LBWH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844231  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C25DE010B35 EU6C25B35 6LBWH  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2277.1 lumens  
Efficiency: N/A  
Efficacy: 76.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 29.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844231

CATALOG NUMBER: LD6C25DE010B35 EU6C25B35 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P844231

CATALOG NUMBER: LD6C25DE010B35 EU6C25B35 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	76989
5°	76964
10°	76374
15°	75857
20°	74708
25°	73002
30°	68732
35°	62198
40°	51947
45°	39803
50°	28187
55°	17768
60°	10021
65°	6499
70°	4248
75°	3114
80°	1863
85°	1887



TEST NUMBER: P844231

CATALOG NUMBER: LD6C25DE010B35 EU6C25B35 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.7	5.8
10°-20°	376.4	16.5
20°-30°	551.9	24.2
30°-40°	574.4	25.2
40°-50°	397.4	17.5
50°-60°	173.0	7.6
60°-70°	53.0	2.3
70°-80°	15.9	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1060.9	46.6
0°-40°	1635.3	71.8
0°-60°	2205.7	96.9
0°-90°	2277.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2277.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1404	
5°	1399	133
15°	1337	376
25°	1207	552
35°	929	574
45°	513	397
55°	186	173
65°	50	53
75°	15	16
85°	3	2
90°	0	



TEST NUMBER: P844231

CATALOG NUMBER: LD6C25DE010B35 EU6C25B35 6LBWH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1404.4
2.5°	1407.4
5°	1398.6
7.5°	1386.8
10°	1372.0
12.5°	1357.3
15°	1336.6
17.5°	1310.0
20°	1280.6
22.5°	1248.1
25°	1206.9
27.5°	1153.7
30°	1085.8
32.5°	1014.9
35°	929.4
37.5°	835.1
40°	725.9
42.5°	616.7
45°	513.4
47.5°	416.0
50°	330.5
52.5°	250.9
55°	185.9
57.5°	132.8
60°	91.4
62.5°	67.9
65°	50.1
67.5°	38.4
70°	26.5
72.5°	20.7
75°	14.7
77.5°	8.8
80°	5.9
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)