

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844308

Luminaire Tested: **LD6C30DE010B35 EU6C30B35 6LBMGPH**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C30DE010B35 EU6C30B35 6LBMGPH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1598.2 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844308

CATALOG NUMBER: LD6C30DE010B35 EU6C30B35 6LBMGPH

Luminous Intensity Polar Plot





TEST NUMBER: P844308

CATALOG NUMBER: LD6C30DE010B35 EU6C30B35 6LBMGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65368
5°	64528
10°	62329
15°	59671
20°	56711
25°	52799
30°	45488
35°	34519
40°	25233
45°	19142
50°	15607
55°	13696
60°	12565
65°	11441
70°	10242
75°	9341
80°	8334
85°	6919



TEST NUMBER: P844308

CATALOG NUMBER: LD6C30DE010B35 EU6C30B35 6LBMGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.2	6.9
10°-20°	295.1	18.5
20°-30°	396.2	24.8
30°-40°	325.0	20.3
40°-50°	195.2	12.2
50°-60°	129.7	8.1
60°-70°	86.9	5.4
70°-80°	46.8	2.9
80°-90°	13.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.4	50.1
0°-40°	1126.4	70.5
0°-60°	1451.3	90.8
0°-90°	1598.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1598.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1192	
5°	1173	110
15°	1051	295
25°	873	396
35°	516	325
45°	247	195
55°	143	130
65°	88	87
75°	44	47
85°	11	13
90°	0	



TEST NUMBER: P844308

CATALOG NUMBER: LD6C30DE010B35 EU6C30B35 6LBMGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1192.4
2.5°	1183.6
5°	1172.6
7.5°	1148.4
10°	1119.7
12.5°	1084.4
15°	1051.4
17.5°	1011.7
20°	972.1
22.5°	928.0
25°	872.9
27.5°	806.8
30°	718.6
32.5°	619.4
35°	515.8
37.5°	427.6
40°	352.6
42.5°	293.2
45°	246.9
47.5°	209.4
50°	183.0
52.5°	160.9
55°	143.3
57.5°	127.9
60°	114.6
62.5°	99.2
65°	88.2
67.5°	75.0
70°	63.9
72.5°	52.9
75°	44.1
77.5°	35.2
80°	26.4
82.5°	19.8
85°	11.0
87.5°	4.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)