

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244500

Luminaire Tested: **LSR8B10D010 EC8B10950 8LBS0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244500  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B10D010 EC8B10950 8LBS0H  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 5000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1139.1 lumens  
Efficiency: N/A  
Efficacy: 111.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244500

CATALOG NUMBER: LSR8B10D010 EC8B10950 8LBS0H

### Luminous Intensity Polar Plot





TEST NUMBER: P244500

CATALOG NUMBER: LSR8B10D010 EC8B10950 8LBS0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	20383
5°	20315
10°	20162
15°	20020
20°	19883
25°	19622
30°	19014
35°	17941
40°	16307
45°	13419
50°	8942
55°	4661
60°	2196
65°	1153
70°	577
75°	405
80°	302
85°	248



TEST NUMBER: P244500

CATALOG NUMBER: LSR8B10D010 EC8B10950 8LBS0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.3	5.5
10°-20°	177.0	15.5
20°-30°	264.8	23.2
30°-40°	296.1	26.0
40°-50°	232.3	20.4
50°-60°	84.8	7.4
60°-70°	17.3	1.5
70°-80°	3.8	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.0	44.2
0°-40°	800.1	70.2
0°-60°	1117.3	98.1
0°-90°	1139.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1139.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	661	
5°	656	62
15°	627	177
25°	577	265
35°	477	296
45°	308	232
55°	87	85
65°	16	17
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P244500

CATALOG NUMBER: LSR8B10D010 EC8B10950 8LBS0H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	661.0
2.5°	660.0
5°	656.3
7.5°	650.9
10°	643.9
12.5°	635.8
15°	627.1
17.5°	617.3
20°	605.9
22.5°	592.5
25°	576.7
27.5°	557.2
30°	534.0
32.5°	506.8
35°	476.6
37.5°	442.7
40°	405.1
42.5°	360.4
45°	307.7
47.5°	248.2
50°	186.4
52.5°	130.7
55°	86.7
57.5°	55.4
60°	35.6
62.5°	23.5
65°	15.8
67.5°	10.1
70°	6.4
72.5°	4.4
75°	3.4
77.5°	2.4
80°	1.7
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)