

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244368

Luminaire Tested: **LSR8B10D010 EC8B109730 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B109730 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 770.0 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244368

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244368

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244368

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	12.8
10°-20°	220.9	28.7
20°-30°	251.1	32.6
30°-40°	147.5	19.2
40°-50°	39.6	5.1
50°-60°	9.4	1.2
60°-70°	2.2	0.3
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.9	74.1
0°-40°	718.4	93.3
0°-60°	767.3	99.7
0°-90°	770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1175	
5°	1092	99
15°	790	221
25°	554	251
35°	230	147
45°	47	40
55°	9	9
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P244368

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1175.4
1°	1168.9
2°	1156.9
3°	1140.0
4°	1118.2
5°	1092.2
6°	1062.8
7°	1029.5
8°	996.2
9°	962.7
10°	930.7
11°	899.5
12°	870.1
13°	842.8
14°	815.5
15°	790.0
16°	765.1
17°	740.4
18°	716.4
19°	692.2
20°	668.6
21°	644.9
22°	622.3
23°	599.9
24°	577.0
25°	554.2
26°	530.5
27°	504.8
28°	477.7
29°	448.1
30°	416.1
32.5°	326.4
35°	229.6
37.5°	151.3
40°	99.1
42.5°	68.4
45°	47.3
47.5°	32.5
50°	21.6
52.5°	14.0
55°	9.4
57.5°	6.2
60°	4.2
62.5°	2.9
65°	2.1



TEST NUMBER: P244368

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.3
70°	0.8
72.5°	0.5
75°	0.5
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)