

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844336

Luminaire Tested: **LD6C30DE010B50 EU6C30B50 6LBCSMMS**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C30DE010B50 EU6C30B50 6LBCSMMS
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3119.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844336

CATALOG NUMBER: LD6C30DE010B50 EU6C30B50 6LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P844336

CATALOG NUMBER: LD6C30DE010B50 EU6C30B50 6LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 110 | 106 | 102 | 99 | 108 | 104 | 100 | 97 | 100 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 89 | 87 | | | | 87 |
| 2 | 101 | 94 | 87 | 82 | 99 | 92 | 86 | 81 | 88 | 84 | 79 | 85 | 81 | 78 | 82 | 79 | 76 | 74 | | | | 74 |
| 3 | 93 | 83 | 75 | 70 | 90 | 81 | 74 | 69 | 79 | 73 | 68 | 76 | 71 | 67 | 73 | 69 | 65 | 63 | | | | 63 |
| 4 | 85 | 74 | 66 | 60 | 83 | 73 | 65 | 59 | 70 | 64 | 58 | 68 | 62 | 58 | 66 | 61 | 57 | 55 | | | | 55 |
| 5 | 79 | 66 | 58 | 52 | 77 | 65 | 57 | 51 | 63 | 56 | 51 | 61 | 55 | 50 | 60 | 54 | 50 | 48 | | | | 48 |
| 6 | 73 | 60 | 52 | 45 | 71 | 59 | 51 | 45 | 57 | 50 | 45 | 56 | 49 | 44 | 54 | 49 | 44 | 42 | | | | 42 |
| 7 | 68 | 55 | 46 | 40 | 66 | 54 | 46 | 40 | 52 | 45 | 40 | 51 | 44 | 40 | 50 | 44 | 39 | 37 | | | | 37 |
| 8 | 63 | 50 | 42 | 36 | 61 | 49 | 41 | 36 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 35 | 33 | | | | 33 |
| 9 | 59 | 46 | 38 | 33 | 57 | 45 | 38 | 32 | 44 | 37 | 32 | 43 | 37 | 32 | 42 | 36 | 32 | 30 | | | | 30 |
| 10 | 55 | 42 | 35 | 30 | 54 | 42 | 34 | 30 | 41 | 34 | 29 | 40 | 34 | 29 | 39 | 33 | 29 | 27 | | | | 27 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 69841 |
| 5° | 69789 |
| 10° | 69755 |
| 15° | 69087 |
| 20° | 68594 |
| 25° | 67909 |
| 30° | 66757 |
| 35° | 65658 |
| 40° | 63712 |
| 45° | 61557 |
| 50° | 57874 |
| 55° | 52395 |
| 60° | 45994 |
| 65° | 38733 |
| 70° | 30310 |
| 75° | 21244 |
| 80° | 11902 |
| 85° | 8240 |



TEST NUMBER: P844336

CATALOG NUMBER: LD6C30DE010B50 EU6C30B50 6LBCSMMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 120.7 | 3.9 |
| 10°-20° | 343.6 | 11.0 |
| 20°-30° | 516.9 | 16.6 |
| 30°-40° | 612.7 | 19.6 |
| 40°-50° | 609.6 | 19.5 |
| 50°-60° | 491.4 | 15.8 |
| 60°-70° | 297.3 | 9.5 |
| 70°-80° | 110.4 | 3.5 |
| 80°-90° | 16.4 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 981.2 | 31.5 |
| 0°-40° | 1593.9 | 51.1 |
| 0°-60° | 2694.9 | 86.4 |
| 0°-90° | 3119.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3119.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1274 | |
| 5° | 1268 | 121 |
| 15° | 1217 | 344 |
| 25° | 1123 | 517 |
| 35° | 981 | 613 |
| 45° | 794 | 610 |
| 55° | 548 | 491 |
| 65° | 299 | 297 |
| 75° | 100 | 110 |
| 85° | 13 | 16 |
| 90° | 0 | |



TEST NUMBER: P844336

CATALOG NUMBER: LD6C30DE010B50 EU6C30B50 6LBCSMMS

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1274.0 |
| 2.5° | 1274.0 |
| 5° | 1268.2 |
| 7.5° | 1264.5 |
| 10° | 1253.1 |
| 12.5° | 1234.0 |
| 15° | 1217.3 |
| 17.5° | 1198.3 |
| 20° | 1175.8 |
| 22.5° | 1152.8 |
| 25° | 1122.7 |
| 27.5° | 1090.5 |
| 30° | 1054.6 |
| 32.5° | 1020.7 |
| 35° | 981.1 |
| 37.5° | 939.5 |
| 40° | 890.3 |
| 42.5° | 842.8 |
| 45° | 794.0 |
| 47.5° | 739.0 |
| 50° | 678.6 |
| 52.5° | 616.1 |
| 55° | 548.2 |
| 57.5° | 487.6 |
| 60° | 419.5 |
| 62.5° | 359.2 |
| 65° | 298.6 |
| 67.5° | 241.9 |
| 70° | 189.1 |
| 72.5° | 141.8 |
| 75° | 100.3 |
| 77.5° | 64.2 |
| 80° | 37.7 |
| 82.5° | 22.6 |
| 85° | 13.1 |
| 87.5° | 5.6 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)