

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844392

Luminaire Tested: **LD6C35DE010B35 EU6C35B35 6LBMB**

Issue Date: 5/7/2024

Test Information

Test Method: LM-79-08
Report Number: P844392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C35DE010B35 EU6C35B35 6LBMB
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1596.0 lumens
Efficiency: N/A
Efficacy: 38.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844392

CATALOG NUMBER: LD6C35DE010B35 EU6C35B35 6LBMB

Luminous Intensity Polar Plot





TEST NUMBER: P844392

CATALOG NUMBER: LD6C35DE010B35 EU6C35B35 6LBMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89																			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71																			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64																			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58																			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53																			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48																			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41																			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65285
5°	64440
10°	62246
15°	59592
20°	56629
25°	52727
30°	45425
35°	34472
40°	25204
45°	19111
50°	15590
55°	13677
60°	12543
65°	11428
70°	10226
75°	9320
80°	8334
85°	6919



TEST NUMBER: P844392

CATALOG NUMBER: LD6C35DE010B35 EU6C35B35 6LBMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.0	6.9
10°-20°	294.7	18.5
20°-30°	395.6	24.8
30°-40°	324.6	20.3
40°-50°	194.9	12.2
50°-60°	129.5	8.1
60°-70°	86.8	5.4
70°-80°	46.7	2.9
80°-90°	13.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	800.3	50.1
0°-40°	1124.9	70.5
0°-60°	1449.3	90.8
0°-90°	1596.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1596.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1191	
5°	1171	110
15°	1050	295
25°	872	396
35°	515	325
45°	246	195
55°	143	130
65°	88	87
75°	44	47
85°	11	13
90°	0	



TEST NUMBER: P844392

CATALOG NUMBER: LD6C35DE010B35 EU6C35B35 6LBMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1190.9
2.5°	1182.0
5°	1171.0
7.5°	1146.8
10°	1118.2
12.5°	1083.0
15°	1050.0
17.5°	1010.4
20°	970.7
22.5°	926.7
25°	871.7
27.5°	805.6
30°	717.6
32.5°	618.5
35°	515.1
37.5°	427.1
40°	352.2
42.5°	292.8
45°	246.5
47.5°	209.1
50°	182.8
52.5°	160.7
55°	143.1
57.5°	127.7
60°	114.4
62.5°	99.1
65°	88.1
67.5°	74.9
70°	63.8
72.5°	52.8
75°	44.0
77.5°	35.2
80°	26.4
82.5°	19.8
85°	11.0
87.5°	4.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)